

# MIC® Unitized Tight-Buffered Cable, Riser

144 F, Single-mode (OS2)

CORNING

Corning Cable Systems MIC® Unitized Riser Cables are designed for use in riser and general purpose environments for intrabuilding backbone installations. These multifiber cables use individually jacketed 900 µm TBII® Buffered Fibers enabling easy, consistent stripping and facilitating termination. The six or 12-fiber subunits allow quick and easy identification and are surrounded by dielectric strength members and protected by a flame-retardant outer jacket.

The all-dielectric cable construction requires no grounding or bonding, making these cables ideal for routing inside buildings including riser shafts, to the telecommunications rooms and workstations. The MIC Unitized Riser Cables meet the application requirements of the National Electrical Code® (NEC®) Article 770 and the ICEA S-83-596 test criteria. They are OFNR and FT-4 listed.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

## Features and Benefits

### 900 µm TBII® Buffered Fibers

Easy, consistent stripping

### 6- or 12-fiber jacketed subunits

Quick and easy identification

### All-dielectric construction

Requires no grounding or bonding

### Flame-retardant jacket

Rugged and durable


## Standards

### Approval and Listings


National Electrical Code® (NEC®) OFNR, CSA FT-4, ICEA S-83-596

### Flame Resistance

UL-1666 (for riser and general building applications)



Part Number: 144E81-T3131-24



Cross Section of Part Number: 144E81-T3131-24

CORNING

# MIC<sup>®</sup> Unitized Tight-Buffered Cable, Riser

144 F, Single-mode (OS2)

CORNING

## Specifications

### General Specifications

Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser
Cable Type	Tight-Buffered
Product Type	Distribution
Flame Rating	Riser (OFNR)
Fiber Category	Single-mode (OS2)

### Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-20 °C to 70 °C (-4 °F to 158 °F)

### Cable Design

Fiber Count	144
Subunit Central Element	Dielectric
Fibers per Subunit	12
Tight buffer color subunit	Blue, Orange, Green
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Tight Buffer Color Subunit, Layer 2	Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Tensile Strength Elements and/or Armoring - Layer 2	Dielectric strength members
Subunit Color	Yellow
Number of Subunits Layer 1	3
Number of Subunits Layer 2	9
Number of Ripcords	13
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Yellow

### Mechanical Characteristics Cable

Max. Tensile Strengths, Short-Term	1320 N (300 lbf)
Max. Tensile Strengths, Long-Term	400 N (90 lbf)
Nominal Outer Diameter	23.7 mm (0.93 in)
Weight	409 kg/km (278 lb/1000 ft)

CORNING

# MIC® Unitized Tight-Buffered Cable, Riser

## 144 F, Single-mode (OS2)

CORNING

### Mechanical Characteristics Cable

Min. Bend Radius Installation	355 mm (14 in)
Min. Bend Radius Operation	237 mm (9.3 in)

### Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

## Fiber Specifications

### Optical Characteristics (cabled)

Fiber Type	Single-mode
Fiber Core Diameter	8.2 µm
Fiber Category	OS2
Fiber Code	E
Performance Option Code	31
Wavelengths	1310 nm / 1383 nm / 1550 nm
Maximum Attenuation	0.65 dB/km / 0.65 dB/km / 0.5 dB/km
Serial 1 Gigabit Ethernet	5000 m / - / -
Serial 10 Gigabit Ethernet	10000 m / - / 40000 m

\* ITU-T G.652 D compliant.

Notes: 1) Improved attenuation and bandwidth options available.  
2) Bend-insensitive single-mode fibers available on request.  
3) *Contact a Corning Cable Systems Customer Care Representative for additional information.*

## Ordering Information

Part Number	144E81-T3131-24
Product Description	MIC® Unitized Tight-Buffered Cable, Riser, 144 F, Single-mode (OS2)

CORNING

# MIC<sup>®</sup> Unitized Tight-Buffered Cable, Riser

144 F, Single-mode (OS2)

The Corning logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

## Notes



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

The Corning logo consists of the word "CORNING" in a large, bold, sans-serif font.