

# FREEDM® One Tight-Buffered Cable, Riser

24 F, 62.5 µm multimode (OM1)

CORNING

Corning Cable Systems FREEDM® One Cables are flame-retardant, UV-resistant, indoor/outdoor cables designed for aerial, duct and direct-buried applications with no need for a transition splice when entering the building. The tight-buffered construction facilitates easier termination for low-fiber-count applications in the local area network (LAN) and eliminates need for fan-out kits. The design features TIA-598 color-coded 900 µm TBII® Buffered Fibers for easy identification, consistent stripping and direct termination. The small diameter and bend radius of the cable allow for easy installation in space-constrained areas while the innovative waterblocking technology is ideal for OSP applications. The all-dielectric cable construction requires no grounding or bonding and the UV-resistant, flame-retardant jacket is rugged, durable and easy to strip.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables while still providing all of the required environmental protection of an indoor/outdoor cable jacket. Black is the standard jacket color using the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

## Features and Benefits

### Waterblocking technology

OSP (outdoor) applications

### Small diameter and bend-radius

Easy installation in space-constrained areas

### Color-coded fibers



Quick and easy identification

### All-dielectric construction

Requires no grounding or bonding

### UV-resistant, flame-retardant jacket

Rugged, durable and easy to strip



## Standards

### Approval and Listings

National Electrical Code®  
(NEC®) OFNR, FT-4

### Design and Test Criteria

ICEA S-104-696

CORNING

# FREEDM® One Tight-Buffered Cable, Riser

24 F, 62.5 µm multimode (OM1)

CORNING

## Specifications

### General Specifications

|                |                                                                           |
|----------------|---------------------------------------------------------------------------|
| Environment    | Indoor/Outdoor Cables                                                     |
| Application    | Aerial, Direct Buried, Duct, General Purpose Horizontal, (Vertical Riser) |
| Cable Type     | Tight-Buffered                                                            |
| Product Type   | Dielectric                                                                |
| Flame Rating   | Riser (OFNR)                                                              |
| Fiber Category | 62.5 µm MM (OM1)                                                          |

### Temperature Range

|              |                                    |
|--------------|------------------------------------|
| Storage      | -40 °C to 70 °C (-40 °F to 158 °F) |
| Installation | -10 °C to 60 °C (14 °F to 140 °F)  |
| Operation    | -40 °C to 70 °C (-40 °F to 158 °F) |

### Cable Design

|                                                     |                                                                                                                                                                                |
|-----------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Central Element                                     | Dielectric                                                                                                                                                                     |
| Fiber Count                                         | 24                                                                                                                                                                             |
| Tight Buffer Color                                  | Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua, Blue*, Orange*, Green*, Brown*, Slate*, White*, Red*, Black*, Yellow*, Violet*, Rose*, Aqua* |
| Tensile Strength Elements and/or Armoring - Layer 1 | Water-swellable strength members                                                                                                                                               |
| Number of Ripcords                                  | 1                                                                                                                                                                              |
| Outer Jacket Material                               | Flame-Retardant, UV-Resistant                                                                                                                                                  |
| Outer Jacket Color                                  | Black                                                                                                                                                                          |

### Mechanical Characteristics Cable

|                                    |                          |
|------------------------------------|--------------------------|
| Weight                             | 60 kg/km (40 lb/1000 ft) |
| Nominal Outer Diameter             | 8.0 mm (.31 in)          |
| Min. Bend Radius Installation      | 120 mm (4.7 in)          |
| Min. Bend Radius Operation         | 40 mm (1.6 in)           |
| Max. Tensile Strengths, Short-Term | 1350 N (300 lbf)         |
| Max. Tensile Strengths, Long-Term  | 400 N (90 lbf)           |

CORNING

# FREEDM® One Tight-Buffered Cable, Riser

24 F, 62.5 µm multimode (OM1)

CORNING

## Chemical Characteristics

|      |                                                           |
|------|-----------------------------------------------------------|
| RoHS | Free of hazardous substances according to RoHS 2002/95/EG |
|------|-----------------------------------------------------------|

## Fiber Specifications

### Optical Characteristics (cabled)

|                                         |                         |
|-----------------------------------------|-------------------------|
| Fiber Core Diameter                     | 62.5 µm                 |
| Fiber Type                              | Multimode               |
| Fiber Category                          | OM1                     |
| Fiber Code                              | K                       |
| Performance Option Code                 | 30                      |
| Wavelengths                             | 850 nm / 1300 nm        |
| Maximum Attenuation                     | 3.4 dB/km / 1.0 dB/km   |
| Min. Overfilled Launch (OFL) Bandwidth  | 200 MHz*km / 500 MHz*km |
| Minimum Effective Modal Bandwidth (EMB) | 220 MHz*km / -          |
| Serial 1 Gigabit Ethernet               | 300 m / 550 m           |
| Serial 10 Gigabit Ethernet              | 33 m / -                |

Notes: 1) Improved attenuation and bandwidth options available.  
2) Bend-insensitive single-mode fibers available on request.  
3) Contact a Corning Cable Systems Customer Care Representative for additional information.

## Ordering Information

|                     |                                                                        |
|---------------------|------------------------------------------------------------------------|
| Part Number         | 024K8F-31130-29                                                        |
| Product Description | FREEDM® One Tight-Buffered Cable, Riser, 24 F, 62.5 µm multimode (OM1) |



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).  
Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING