

FREEDM® One Tight-Buffered Cable, Riser

24 F, 50 µm multimode (OM4)

CORNING

Corning Cable Systems FREEDM® One Cables are flame-retardant, UV-resistant, indoor/outdoor cables designed for aerial, duct and direct-buried applications with no need for a transition splice when entering the building. The tight-buffered construction facilitates easier termination for low-fiber-count applications in the local area network (LAN) and eliminates need for fan-out kits. The design features TIA-598 color-coded 900 µm TBII® Buffered Fibers for easy identification, consistent stripping and direct termination. The small diameter and bend radius of the cable allow for easy installation in space-constrained areas while the innovative waterblocking technology is ideal for OSP applications. The all-dielectric cable construction requires no grounding or bonding and the UV-resistant, flame-retardant jacket is rugged, durable and easy to strip.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables while still providing all of the required environmental protection of an indoor/outdoor cable jacket. Black is the standard jacket color using the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

Features and Benefits

Waterblocking technology

OSP (outdoor) applications

Small diameter and bend-radius

Easy installation in space-constrained areas

Color-coded fibers


Quick and easy identification

All-dielectric construction


Requires no grounding or bonding

UV-resistant, flame-retardant jacket

Rugged, durable and easy to strip



Part Number: 024T8F-31190-29



Cross Section of Part Number: 024T8F-31190-29

Standards

Approval and Listings

National Electrical Code®
(NEC®) OFNR, FT-4

Design and Test Criteria

ICEA S-104-696

CORNING

FREEDM® One Tight-Buffered Cable, Riser

24 F, 50 µm multimode (OM4)

CORNING

Specifications

General Specifications

Environment	Indoor/Outdoor Cables
Application	Aerial, Direct Buried, Duct, General Purpose Horizontal, (Vertical Riser)
Cable Type	Tight-Buffered
Product Type	Dielectric
Flame Rating	Riser (OFNR)
Fiber Category	50 µm MM (OM4)

Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-40 °C to 70 °C (-40 °F to 158 °F)

Cable Design

Central Element	Dielectric
Fiber Count	24
Tight Buffer Color	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua, Blue*, Orange*, Green*, Brown*, Slate*, White*, Red*, Black*, Yellow*, Violet*, Rose*, Aqua*
Tensile Strength Elements and/or Armoring - Layer 1	Water-swellable strength members
Number of Ripcords	1
Outer Jacket Material	Flame-Retardant, UV-Resistant
Outer Jacket Color	Black

Mechanical Characteristics Cable

Weight	60 kg/km (40 lb/1000 ft)
Nominal Outer Diameter	8.0 mm (.31 in)
Min. Bend Radius Installation	120 mm (4.7 in)
Min. Bend Radius Operation	40 mm (1.6 in)
Max. Tensile Strengths, Short-Term	1350 N (300 lbf)
Max. Tensile Strengths, Long-Term	400 N (90 lbf)

CORNING

FREEDM® One Tight-Buffered Cable, Riser

24 F, 50 µm multimode (OM4)

CORNING

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Fiber Specifications

Optical Characteristics (cabled)

Fiber Type	Multimode
Fiber Core Diameter	50 µm
Fiber Category	OM4
Fiber Code	T
Performance Option Code	90
Wavelengths	850 nm / 1300 nm
Maximum Attenuation	2.8 dB/km / 1 dB/km
Min. Overfilled Launch (OFL) Bandwidth	3500 MHz*km / 500 MHz*km
Minimum Effective Modal Bandwidth (EMB)	4700 MHz*km / -
Serial 1 Gigabit Ethernet	1100 m / 600 m
Serial 10 Gigabit Ethernet	550 m / -

* Assumes 1.0 dB maximum total connector/splice loss.

* Meets 0.75 ns optical skew when used in all Corning Cable Systems Plug & Play™/Pretium EDGE® Systems Solutions.

Notes: 1) 50 µm multimode fiber macrobend loss ≤ 0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.

2) Improved attenuation and bandwidth options available.

3) Bend-insensitive single-mode fibers available on request.

4) Contact a Corning Cable Systems Customer Care Representative for additional information.

Ordering Information

Part Number	024T8F-31190-29
Product Description	FREEDM® One Tight-Buffered Cable, Riser, 24 F, 50 µm multimode (OM4)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING