

Closet Connector Housing (CCH) Module, pigtailed, SC Connectors

Duplex, UPC, 12 F, Single-mode (OS2)

CORNING

Corning Cable Systems Closet Connector Housing (CCH) Pigtail Modules accommodate all industry-standard connector adapter types including the LC, ST[®] Compatible, SC, SC duplex, FC and MT-RJ, as well as the keyed LC. Like LANscape[®] Solutions panels, the modules are the same size for 6-, 8-, 12-, 16-, and 24-fiber capacities. Each module provides strain-relief for the pigtail and offers the advantage of greater protection to the cables and connectors being installed when the pigtails will be routed and spliced in a separate housing. Available with both ribbon and 900-um tight buffer (MIC) cable types, each CCH module is factory terminated and tested. Each module is shipped assembled with adapters and connectorized pigtails installed to the customer's specifications.

Many of our fiber optic hardware products are highly configurable. If you don't see what you are looking for here, please review the ordering matrix contained in the family spec sheet found on the right, or contact customer care at 1-800-743-2671.



Features

- **Factory-terminated and -tested**
Guaranteed performance
- **Compatible with other LANscape[®] Solutions**
System consistency
- **Strain-relief for pigtail**
Fiber protection and reliability
- **Durable construction**
Protection for connectors and adapters

Specifications

General Specifications	
Application	Enterprise Networks, Data Center
Product Type	Panels & Modules
Fiber Category	Single-mode (OS2)
Cable Type Stubbed	MIC [®] Cable subunit

Closet Connector Housing (CCH) Module, pigtailed, SC Connectors

Duplex, UPC, 12 F, Single-mode (OS2)

CORNING

Design - Hardware

Connector Type A	SC
Connector Polish	UPC
Fiber Count	12
Number of Adapters per Panel	12
Pigtail Length	9.84 ft (3 m)

Optical Specification - Hardware

Module insertion loss, typical (by 1310 nm)	0.15 dB
Module Insertion Loss, Max (by 1310nm)	0.4 dB

Design Adapter

Adapter Housing Color	Blue
Adapter Housing Material	Composite
Adapter Style	Standard
Adapter Type	SC duplex
Insert Material	Ceramic

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Ordering Information

Part Number	CCH-RM12-59-P03RH
Product Description	Closet Connector Housing (CCH) Module, pigtailed, SC connectors, Duplex, UPC, 12 F, Single-mode (OS2)

Closet Connector Housing (CCH) Module, pigtailed, SC Connectors

Duplex, UPC, 12 F, Single-mode (OS2)



Shipping Information

Units per Delivery	1/1
Package Contents	CCH Module with 3 m pigtail; installation guide; two 1/8 x 4-in tie wraps, white; 3/16-in outer diameter Teflon spiral wrap, 10 ft



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.