

FREEDM® One Interlocking Armored Riser Cables

CORNING

Features and Benefits

Waterblocking technology
OSP applications

Flexible, interlocking armor design
Seven times crush protection compared to unarmored cables

UV-resistant, flame-retardant jacket
Rugged, durable and easy to strip

Standards


Approval and Listings	National Electrical Code® (NEC®) OFCR, CSA FT-4, ICEA S-104-696
Flame Resistance	UL-1666 (for riser and general building applications)

Corning Cable Systems FREEDM® One Interlocking Armored Cables are flame-retardant, indoor/outdoor, cables designed for interbuilding and intrabuilding back-bone installations that eliminate the need for a transition splice when entering the building. Encased in a spirally wrapped, aluminum interlocking armor for ruggedness and superior crush resistance, these cables are ideal for industrial and heavy traffic areas and installations requiring extra protection for optical cables. These cables are protected against water penetration by innovative water-blocking technology, making it ideal for OSP applications. The flexible, interlocking armored design offers over seven times the crush protection compared to unarmored cables (as characterized to ICEA-696) and allows easy one step installation, thereby reducing the overall installation costs. The UV-resistant, flame-retardant jacket is rugged, durable and easy to strip.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables while still providing all of the required environmental protection of an indoor/outdoor cable jacket. Black is the standard jacket color using the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.



FREEDM® One Interlocking Armored Riser Cables,
12-Fibers



FREEDM® One Interlocking Armored Riser Cables,
12-Fibers


CORNING

FREEDM® One Interlocking Armored Riser Cables

CORNING



FREEDM® One Interlocking Armored Riser Cables, 24-Fibers



FREEDM® One Interlocking Armored Riser Cables, 24-Fibers

Specifications

Temperature Range	
Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-40 °C to 70 °C (-40 °F to 158 °F)

* Corning Cable Systems recommends storing indoor/outdoor cable in a proper temperature environment prior to installation to allow the cable temperature to meet installation temperature range specifications for best installation results.

Mechanical Characteristics Cable					
Fiber Count	Product Type	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Weight
2	Interlocking armor	11.5 mm (.45 in)	78 mm (3.1 in)	52 mm (2.0 in)	107 kg/km (72 lb/1000 ft)
4	Interlocking armor	11.5 mm (.45 in)	83 mm (3.2 in)	55 mm (2.2 in)	110 kg/km (74 lb/1000 ft)
6	Interlocking armor	11.5 mm (.45 in)	83 mm (3.2 in)	55 mm (2.2 in)	112 kg/km (75 lb/1000 ft)
12	Interlocking armor	12.5 mm (.49 in)	98 mm (3.8 in)	65 mm (2.6 in)	131 kg/km (88 lb/1000 ft)

CORNING

FREEDM® One Interlocking Armored Riser Cables

CORNING

Fiber Count	Product Type	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Weight
18	Interlocking armor	13.3 mm (.52 in)	111 mm (4.4 in)	74 mm (2.9 in)	153 kg/km (103 lb/1000 ft)
24	Interlocking armor	14.6 mm (.57 in)	120 mm (4.7 in)	80 mm (3.1 in)	173 kg/km (117 lb/1000 ft)

Chemical Characteristics

RoHS

Free of hazardous substances according to RoHS 2002/95/EG

CORNING

FREEDM® One Interlocking Armored Riser Cables

CORNING

Transmission Performance

Fiber Type	Multimode	Multimode	Multimode	Multimode	Multimode	Single-mode	Bend-Improved Single-mode (OS2)
Fiber Core Diameter (μm)	62.5	50	50	50	50	8.2	9
Fiber Category	OM1	OM2	OM3	OM4	OM4 Extended Distance	OS2	OS2
Fiber Code	K	T	T	T	T	E	H
Performance Option Code	30	31	80	90	91	31	31
Wavelengths (nm)	850 / 1300	850 / 1300	850 / 1300	850 / 1300	850 / 1300	1310 / 1383 / 1550	1310 / 1383 / 1550
Maximum Attenuation (dB/km)	3.4 / 1.0	2.8 / 1	2.8 / 1	2.8 / 1	2.8 / 1	0.65 / 0.65 / 0.5	0.65 / 0.65 / 0.5
Serial 1 Gigabit Ethernet (m)	300 / 550	750 / 600	1000 / 600	1100 / 600	1100 / 600	5000 / - / -	5000 / - / -
Serial 10 Gigabit Ethernet (m)	33 / -	150 / -	300 / -	550 / -	600 / -	10000 / - / 40000	10000 / - / 40000
Min. Overfilled Launch (OFL) Bandwidth (MHz*km)	200 / 500	700 / 500	1500 / 500	3500 / 500	3500 / 500		
Minimum Effective Modal Bandwidth (EMB) (MHz*km)	220 / -	950 / -	2000 / -	4700 / -	5350 / -		
Induced Attenuation @ 7.5 mm Radius (dB)			< 30 up to 80				

* Assumes 1.0 dB maximum total connector/splice loss.

* Assumes 0.7 dB maximum total connector/splice loss.

* Meets 0.75 ns optical skew when used in all Corning Cable Systems Plug & Play™/Pretium EDGE® Systems Solutions.

* ITU-T G.652 D compliant.

* ITU-T G.652 D and ITU-T G.657 A1 compliant

Notes: 1) Improved attenuation and bandwidth options available.

2) Bend-insensitive single-mode fibers available on request.


3) Contact a Corning Cable Systems Customer Care Representative for additional information.

CORNING

FREEDM® One Interlocking Armored Riser Cables

CORNING

Ordering Information | Contact Customer Care at 1-800-743-2671 for other options.



1 Select fiber count.

Standard offerings:

002 006 018
004 012 024

2 Select fiber code.

K = 62.5 μ m multimode,
OM1
T = 50 μ m multimode,
OM2, OM3, OM4, OM4+
E = Single-mode, OS2
SMF-28e®

3 Defines cable type.

8 = FREEDM® One Cable

4 Defines outer jacket.

F = Indoor/outdoor riser

5 Defines fiber placement.

3 = Standard for FREEDM
One Plenum Cable

6 Defines length markings.

1 = Markings in feet
(standard) for single-layer
design.

7 Defines tensile strength.

1 = See Specifications.

8 Select performance
option code.

30 = 62.5 μ m multimode, OM1
31 = 50 μ m multimode, OM2
80 = 50 μ m multimode, OM3
90 = 50 μ m multimode, OM4
91 = 50 μ m multimode, OM4+
31 = Single-mode, OS2
(Max. attenuation .65 / .65 dB/km)

9 Defines cable type.

- = FREEDM® One Cable

10 Defines special
requirements.

A1 = Aluminum interlocking
armor with riser-rated
jacket

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables while still providing all of the required environmental protection of an indoor/outdoor cable jacket. Black is the standard jacket color using the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING