

LANscape® Pretium™ Solutions

Plug & Play™ Systems U-Clip Strain-Relief and Accessory Brackets

Part Number Reference Sheet



PC1-RJ-STR

Photo LAN1363



PC2-STRN

Photo LAN1364



PC4-RJ-STR

Photo LAN1366

Mounting of Plug & Play™ Systems trunks using the integrated U-clip strain-relief feature is available utilizing the following brackets. The following tables detail whether a separate bracket is required for the housing (accessory) or if it is standard with the housing. The quantity of Plug & Play Systems MTP® Connector trunks that can be mounted are shown by fiber count.

RACK-MOUNTABLE HOUSING STRAIN-RELIEF BRACKETS

Hardware			12-24 Fibers		36-48 Fibers Non-Armored and Armored	72-96 Fibers Non-Armored and Armored	144 Fibers	
			Non-Armored	Armored			Non-Armored	Armored
PCH-01U								
1U Strain-Relief Bracket (2) Accessory	PC1-RJ-STR		3	2	2	2	2	2
PCH-02U								
2U Strain-Relief Bracket Accessory	PC2-STRN		4	2	2	2	2	2
PCH-04U								
4U Strain-Relief Bracket (2) Accessory	PC4-RJ-STR		3	2	2	2	2	2
Strain-Relief Rear Plate to install inside of PCH	PC4-RJ-PLT	Accessory	12	0	0	0	0	0
PCH-M3-01U								
Strain-Relief Integral to Housing	Standard	N/A	6	0	0	0	0	0
96-Fiber (Example P/N: HD1A-U96-05-70S)								
Strain-Relief Integral to Housing	Standard	N/A	8*	4**	4**	2***	N/A	N/A

A (2) in the part description indicates two brackets are included.

* Using up to (4) U-Clip locations each in the left and right floor of the shelf

** Using up to (2) U-Clip locations each in the left and right floor of the shelf

*** Two rear flanges (one each at the left and right rear corners of the shelf) accommodate (1) trunk U-Clip each

WALL-MOUNTABLE HOUSING STRAIN-RELIEF BRACKETS

Hardware			12-24 Fibers		36-48 Fibers Non-Armored and Armored	72-96 Fibers Non-Armored and Armored	144 Fibers	
			Non-Armored	Armored			Non-Armored	Armored
PWH-02P								
Interior Strain-Relief Bracket	Standard	N/A	3	1	1	1	1	1
PWH-04P								
Interior Strain-Relief Bracket	Standard	N/A	4	2	2	2*	2*	0
PWH-06P								
Interior Strain-Relief Bracket	Standard	N/A	4	2	2	2*	2*	0
PWH-12P								
Interior Strain-Relief Bracket	Standard	N/A	8	4	4	4*	4*	0
Exterior Strain-Relief Bracket for PWH-02P, -04P, -06P, -12P								
Exterior Strain-Relief Bracket (2)	Accessory	PWH-RJSR	3	2	2	1	1	1

A (2) in the part description indicates two brackets are included.

* Requires removal and reinstallation of a bracket via two nuts

CORNING
LANscape®
Pretium™ Solutions



PC4-RJ-PLT

Photo LAN1365



PWH-RJSR

Photo LAN1367



CDF-RJ-BKT

Photo LAN1357

LANscape® Pretium™ Solutions

Plug & Play™ Systems U-Clip Strain-Relief and Accessory Brackets

Part Number Reference Sheet



CDF-RJ06-BKT

Photo LAN1358



CDF-RJ07-BKT

Photo LAN1359



CDF-RJ12-BKT

Photo LAN1360



RBC-02P

Photo LAN1368

FRAME-MOUNTABLE STRAIN-RELIEF BRACKETS


Frame Mounted Strain-Relief Bracket	12-24 Fibers		36-48 Fibers	72-96 Fibers	144 Fibers	
	Non-Armored	Armored	Non-Armored and Armored	Non-Armored and Armored	Non-Armored	Armored
Strain-Relief Bracket (2) Accessory CDF-RJ-BKT	1	1	1	0**	0**	0
6-in Strain-Relief Bracket Accessory CDF-RJ06-BKT	6	3	3	3	3	3
7-in Strain-Relief Bracket Accessory CDF-RJ07-BKT	7	4	4	4	4	4
12-in Strain-Relief Bracket Accessory CDF-RJ12-BKT	12	6	6	6	6	6
18-in Strain-Relief Bracket Accessory CDF-RJ18-BKT	18	9	9	9	9	9

A (2) in the part description indicates two brackets are included.

** May accommodate one 72- to 144-Fiber trunk depending on the IBU used and location on the rack


ACCESSORY BRACKETS/PANELS FOR PLUG & PLAY™ SYSTEMS

Part Number	Description
RBC-02P	Frame-Mountable Bracket, capacity for up to two (2) Plug & Play Systems modules or adapter panels
CPP-01U-PNL	1U Rack-Mountable Panel, capacity for up to two (2) Plug & Play Systems modules or adapter panels
CPP-M3-01U	1U Rack-Mountable Panel, capacity for up to three (3) Plug & Play Systems modules or adapter panels



CPP-01U-PNL

Photo LAN1361



CPP-M3-01U

Photo LAN1362