


MIC® 250 Distribution Cable, Plenum

72 F, Single-mode (OS2)

CORNING

Corning Cable Systems MIC® 250 Cables utilize 250 µm color-coded optical fibers, surrounded by dielectric strength members with a flexible, flame retardant outer jacket. These cables are ideal for creating multifiber preconnectorized assemblies as the 12-fiber groupings enable efficient compatibility with multifiber connectors. The flexible, flame-retardant jacket and non-preferential bend axis allow easy installation in space-constrained areas and the all-dielectric cable construction requires no grounding or bonding. The MIC 250 Cables meet the application requirements of the National Electrical Code® (NEC Article 770) and are OFNP and FT-6 listed for plenum, riser or general purpose applications.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.



Part Number: 072ED8-T1331-20

Features and Benefits

Color-coded fibers

Quick and easy identification

12-fiber groupings

Compatibility with multifiber connectors

All-dielectric construction

Requires no grounding or bonding


Standards

Approval and Listings

National Electrical Code® (NEC®) OFNP, CSA FT-6, ICEA S-83-596

Flame Resistance

NFPA 262 (for plenum, riser and general building applications)



Cross Section of Part Number: 072ED8-T1331-20

CORNING

MIC® 250 Distribution Cable, Plenum

72 F, Single-mode (OS2)

CORNING

Specifications

General Specifications

Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser, Plenum
Cable Type	Loose Tube
Product Type	Distribution
Flame Rating	Plenum (OFNP)
Fiber Category	Single-mode (OS2)

Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	0 °C to 60 °C (32 °F to 140 °F)
Operation	0 °C to 70 °C (32 °F to 158 °F)

Cable Design

Central Element	Jacketed GRP
Fiber Count	72
Fibers per Subunit	12
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Subunit Jacket Material	Flame-retardant
Subunit Color	Yellow
Number of Subunits	6
Number of Ripcords	1
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Yellow

Mechanical Characteristics Cable

Weight	132 kg/km (88.7 lb/1000 ft)
Nominal Outer Diameter	12 mm (0.48 in)
Max. Tensile Strengths, Short-Term	660 N (150 lbf)
Max. Tensile Strengths, Long-Term	200 N (45 lbf)

CORNING

MIC® 250 Distribution Cable, Plenum

72 F, Single-mode (OS2)

CORNING

Mechanical Characteristics Cable

Min. Bend Radius Installation	180 mm (7.1 in)
Min. Bend Radius Operation	120 mm (4.7 in)

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Fiber Specifications

Optical Characteristics (cabled)

Fiber Type	Single-mode
Fiber Core Diameter	9 µm
Fiber Category	OS2
Fiber Code	E
Performance Option Code	01
Wavelengths	1310 nm / 1383 nm / 1550 nm
Maximum Attenuation	0.65 dB/km / 0.65 dB/km / .5 dB/km
Serial 1 Gigabit Ethernet	5000 m / - / -
Serial 10 Gigabit Ethernet	10000 m / - / 40000 m

* ITU-T G.652 D compliant.

* Meets 0.75 ns optical skew when used in all Corning Cable Systems Plug & Play™/Pretium EDGE® Systems Solutions.

Notes: 1) Improved attenuation and bandwidth options available.
2) Bend-insensitive single-mode fibers available on request.
3) Contact a Corning Cable Systems Customer Care Representative for additional information.

Ordering Information

Part Number	072ED8-T1331-20
Product Description	MIC® 250 Distribution Cable, Plenum, 72 F, Single-mode (OS2)

CORNING

MIC[®] 250 Distribution Cable, Plenum

72 F, Single-mode (OS2)

The Corning logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

Notes



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

The Corning logo consists of the word "CORNING" in a large, bold, sans-serif font.