

# Splice Tray, RTV Splices

Reduced length, 0.2-in, 12 F

CORNING

Corning Cable Systems splice trays use proven designs and fiber organization technology to provide optimum physical protection for fusion and mechanical splicing methods. The trays are engineered for use with indoor or outdoor splice hardware with both loose tube and tight-buffered optical cable designs.

The metal-tray series consists of a rugged aluminum base and cover with crimpable metal tabs for buffer tube strain-relief. Additional strain-relief points are available for securing buffer tubes or pigtails to the trays using cable ties. The black powder coating allows easy fiber identification and additional protection. Designed for use with Corning Cable Systems interconnection hardware and splice closures, these splice trays are an integral part of a complete splicing system.

**Many of our fiber optic hardware products are highly configurable. If you don't see what you are looking for here, please review the ordering matrix contained in the family spec sheet found on the right, or contact customer care at 1-800-743-2671.**

## Features and Benefits

**Metal trays powder coated**  
Ruggedness and durability

**Clear plastic covers**  
Fiber visibility for inspection

**Fiber loop retention**  
Controls the bend-radius

**Positive holding action**  
Maximum splice protection



Part Number: M67-060



Part Number: M67-060

CORNING

# Splice Tray, RTV Splices

Reduced length, 0.2-in, 12 F

CORNING

## Specifications

### General Specifications

Application	Central Office, CATV environments, Carrier Networks, Enterprise Networks
Product Type	Splice Trays
Technology	Fusion Splice

### Design - Hardware

Splice Protectors Type	RTV (Room Temperature Vulcanizing) Fusion Sealant
Splice Tray Category	2R
Splice Tray Type	Standard with organizers for RTV splice protectors
Splice Tray Capacity Single Fiber	12 Splices

### Mechanical Characteristics

Dimensions (LxWxD)	7.3 in x 3.5 in x 0.2 in185 mm x 89 mm x 5 mm
--------------------	---

### Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

## Ordering Information

Part Number	M67-060
Product Description	Splice Tray, RTV splices, reduced length, 0.2-in, 12 F

## Shipping Information

Units per Delivery	1/1
Package Contents	Installation Guide; splice tray base with splice holder; splice tray cover

CORNING

# Splice Tray, RTV Splices

Reduced length, 0.2-in, 12 F

CORNING

## Notes



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING