

# ALTOS® Loose Tube, Gel-Free Cable

144 F, Single-mode (OS2)

CORNING

Corning Cable Systems ALTOS® All-Dielectric Gel-Free Cables are designed for outdoor and limited indoor use for campus backbones in lashed aerial and duct installations. The loose tube gel-free design is fully waterblocked using craft-friendly, water-swellable materials, which means cable access is simple and no clean up is required. The flexible craft-friendly buffer tubes are easy to route in closures and the SZ-stranded, loose tube design isolates fibers from installation and environmental rigors while allowing easy midspan access. The all-dielectric cable construction requires no bonding or grounding and these cables have a medium-density polyethylene jacket that is rugged, durable and easy to strip.

## Features and Benefits

### Gel-free waterblocking technology

Craft-friendly cable preparation

### Medium-density polyethylene jacket

Rugged, durable and easy to strip while providing superior protection against UV radiation, fungus, abrasion and other environmental factors

### All-dielectric construction

Requires no grounding or bonding


## Standards

### Common Installations


Outdoor lashed aerial and duct; indoor when installed according to National Electrical Code® (NEC®) Article 770

### Design and Test Criteria

ANSI/ICEA S-87-640



Part Number: 144EU4-T4101D20



Cross Section of Part Number: 144EU4-T4101D20

# ALTOS® Loose Tube, Gel-Free Cable

144 F, Single-mode (OS2)

CORNING

## Specifications

### General Specifications

Environment	Outdoor
Application	Aerial, Duct
Cable Type	Loose Tube
Product Type	Dielectric
Fiber Category	Single-mode (OS2)

### Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-30 °C to 70 °C (-22 °F to 158 °F)
Operation	-40 °C to 70 °C (-40 °F to 158 °F)

### Cable Design

Central Element	Dielectric
Fiber Count	144
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Fibers per Tube	12
Number of Tube Positions	12
Number of Active Tubes	12
Buffer Tube Color Coding	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Buffer Tube Diameter	2.5 mm (0.1 in)
Tape	Water-swellaable
Number of Ripcords	1
Outer Jacket Material	Polyethylene (PE)
Outer Jacket Color	Black

### Mechanical Characteristics Cable

Max. Tensile Strengths, Short-Term	2700 N (600 lbf)
Max. Tensile Strengths, Long-Term	890 N (200 lbf)
Weight	162 kg/km (109 lb/1000 ft)
Nominal Outer Diameter	15.8 mm (0.62 in)

CORNING

# ALTOS® Loose Tube, Gel-Free Cable

144 F, Single-mode (OS2)

CORNING

## Mechanical Characteristics Cable

Min. Bend Radius Installation	237 mm (9.3 in)
Min. Bend Radius Operation	158 mm (6.2 in)

## Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

## Fiber Specifications

### Optical Characteristics (cabled)

Fiber Type	Single-mode
Fiber Core Diameter	8.2 µm
Fiber Category	OS2
Fiber Code	E
Performance Option Code	01
Wavelengths	1310 nm / 1383 nm / 1550 nm
Maximum Attenuation	0.4 dB/km / 0.4 dB/km / 0.3 dB/km
Serial 1 Gigabit Ethernet	5000 m / - / -
Serial 10 Gigabit Ethernet	10000 m / - / 40000 m

\* ITU-T G.652 D compliant.

\* Meets 0.75 ns optical skew when used in all Corning Cable Systems Plug & Play™/Pretium EDGE® Systems Solutions.

Notes: 1) Improved attenuation and bandwidth options available.  
2) Bend-insensitive single-mode fibers available on request.  
3) Contact a Corning Cable Systems Customer Care Representative for additional information.

## Ordering Information

Part Number	144EU4-T4101D20
Product Description	ALTOS® Loose Tube, Gel-Free Cable, 144 F, Single-mode (OS2)

CORNING

# ALTOS® Loose Tube, Gel-Free Cable

144 F, Single-mode (OS2)

CORNING

## Notes



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING