

# UniCam® Keyed LC Connector, 50 µm multimode (OM2)

Red

CORNING

Corning Cable Systems Keyed LC Connector Solution offers mechanical network security for organizations desiring to segregate networks due to privacy or security concerns. Utilizing the LC small-form-factor (SFF) format for optical fiber cabling, the keyed LC solution provides physical separation for up to eight networks, applications, or organizations. Eight color-coded key combinations prevent inadvertent or unauthorized access to networks and provide fast and easy network identification. Keyed connectors on the front and back of the patch panel area are used to match access rights to the proper network. The keyed features cannot be duplicated with standard LC components, thereby preventing violation of network security.

## Features and Benefits

### Keyed connector solution

Front and rear security in network panel

### Eight color-coded mechanical key positions

Prevents mismatch of networks

### Broad operating temperature (-40° to +75°C)

Utility and flexibility

### Factory-polished end face

Consistent optical performance

### Fast termination and no consumables

Low installation cost

### Minimum insertion loss

Optimum optical performance



Part Number: 95-050-KR

## Standards

### Approval and Listings

Passed EIA/TIA 568-B.3

### Intermateability

Connectors are FOCIS compliant with TIA/EIA 604-10A and IEC61754-20

CORNING

# UniCam® Keyed LC Connector, 50 µm multimode (OM2)

Red

CORNING

## Specifications

General Specifications	
Technology	No-Epoxy/No-Polish
Keyed	Yes
Product Type	Field-Installable Connectors
Corning Logo	Yes
Packaging	Single Pack
Fiber Category	50 µm MM (OM2)

Temperature Range	
Operation	-40 °C to 75 °C exceeding EIA/TIA 568-B.3 (-40 °F to 167 °F exceeding EIA/TIA 568-B.3)

Chemical Characteristics	
RoHS	Free of hazardous substances according to RoHS 2002/95/EG

## Ordering Information

Part Number	95-050-KR
Product Description	UniCam® Keyed LC Connector, 50 µm multimode (OM2), ceramic ferrule, single pack, red housing, red boot

## Shipping Information

Units per Delivery	1/1
Package Contents	Keyed connector, trigger, crimp band, boot (900 µm), boot (3.0 mm), boot (2.0 mm)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING