

ALTOS® All-Dielectric Gel-Free Cables

CORNING

Features and Benefits

Fully waterblocked loose tube gel-free design

Simple access and no clean up

Medium-density polyethylene jacket

Rugged, durable and easy to strip while providing superior protection against UV radiation, fungus, abrasion and other environmental factors

All-dielectric cable construction

Requires no grounding or bonding

Available in 62.5 μm , 50 μm , single-mode (including bend-insensitive and non-zero dispersion shifted fiber (NZ-DSF) options) and hybrid versions

Ready for any application including Gigabit Ethernet and 10 Gigabit Ethernet

Corning Cable Systems ALTOS® All-Dielectric Gel-Free Cables are designed for outdoor and limited indoor use for campus backbones in lashed aerial and duct installations. The loose tube gel-free design is fully waterblocked using craft-friendly, water-swellaable materials, which means cable access is simple and no clean up is required. The flexible craft-friendly buffer tubes are easy to route in closures and the SZ-stranded, loose tube design isolates fibers from installation and environmental rigors while allowing easy midspan access. The all-dielectric cable construction requires no bonding or grounding and these cables have a medium-density polyethylene jacket that is rugged, durable and easy to strip.


Standards

Common Installations Outdoor lashed aerial and duct; indoor when installed according to National Electrical Code® (NEC®) Article 770

Design and Test Criteria ANSI/ICEA S-87-640
Telcordia GR-20
RDUP PE-90 listed




ALTOS® All-Dielectric, Gel-Free Cables, 36-Fibers




ALTOS® All-Dielectric, Gel-Free Cables, 36-Fibers

ALTOS® All-Dielectric Gel-Free Cables

CORNING



ALTOS® All-Dielectric, Gel-Free Cables, 288-Fibers



ALTOS® All-Dielectric, Gel-Free Cables, 288-Fibers

Specifications

Temperature Range	
Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-30 °C to 70 °C (-22 °F to 158 °F)
Operation	-40 °C to 70 °C (-40 °F to 158 °F)

* Corning Cable Systems recommends storing cable in a proper temperature environment prior to installation to allow the cable temperature to meet installation temperature range specifications for best installation results.

Mechanical Characteristics Cable	
Max. Tensile Strengths, Short-Term	2700 N (600 lbf)
Max. Tensile Strengths, Long-Term	890 N (200 lbf)

Fiber Count	Product Type	Maximum Fibers per Tube	Number of Tube Positions	Number of Active Tubes	Weight	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation
2 - 72	Dielectric	12	6	1 - 6	73 kg/km (49 lb/1000 ft)	10.5 mm (0.41 in)	158 mm (6.2 in)	105 mm (4.1 in)
84 - 96	Dielectric	12	8	7 - 8	98 kg/km (66 lb/1000 ft)	12.2 mm (0.48 in)	183 mm (7.2 in)	122 mm (4.8 in)
108 - 144	Dielectric	12	12	9 - 12	162 kg/km (109 lb/1000 ft)	15.8 mm (0.62 in)	237 mm (9.3 in)	158 mm (6.2 in)

CORNING

ALTOS® All-Dielectric Gel-Free Cables

CORNING

Fiber Count	Product Type	Maximum Fibers per Tube	Number of Tube Positions	Number of Active Tubes	Weight	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation
156 - 216	Dielectric	12	18	13 - 18	147 kg/km (99 lb/1000 ft)	16 mm (0.63 in)	240 mm (9.4 in)	160 mm (6.3 in)
228 - 288	Dielectric	12	24	19 - 24	196 kg/km (131 lb/1000 ft)	18.2 mm (0.72 in)	273 mm (10.7 in)	182 mm (7.2 in)

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Transmission Performance

Fiber Type	Multimode	Multimode	Multimode	Multimode	Single-mode	Single-mode
Fiber Core Diameter (µm)	62.5	50	50	50	8.2	8.2
Fiber Category	OM1	OM2	OM3	OM4	OS2	OS2
Fiber Code	K	T	T	T	E	E
Performance Option Code	30	31	80	90	01	00
Wavelengths (nm)	850 / 1300	850 / 1300	850 / 1300	850 / 1300	1310 / 1383 / 1550	1310 / 1383 / 1550
Maximum Attenuation (dB/km)	3.4 / 1.0	3.0 / 1.0	3.0 / 1.0	3.0 / 1.0	0.4 / 0.4 / 0.3	0.35 / 0.35 / 0.25
Serial 1 Gigabit Ethernet (m)	300 / 550	750 / 600	1000 / 600	1100 / 600	5000 / - / -	5000 / - / -
Serial 10 Gigabit Ethernet (m)	33 / -	150 / -	300 / -	550 / -	10000 / - / 40000	10000 / - / 40000
Min. Overfilled Launch (OFL) Bandwidth (MHz*km)	200 / 500	700 / 500	1500 / 500	3500 / 500		
Minimum Effective Modal Bandwidth (EMB) (MHz*km)	220 / -	950 / -	2000 / -	4700 / -		

* Single-mode (OS2) fiber is ITU-T G.652.D compliant.

* OM4 Multimode fiber 10 Gigabit Ethernet distance assumes 1.0 dB maximum total connector/splice loss.


- Notes:
- 1) Improved attenuation and bandwidth options available.
 - 2) Bend-insensitive single-mode fibers available on request.
 - 3) Contact a Corning Cable Systems Customer Care Representative for additional information.
 - 4) 50 µm multimode fiber macrobend loss ≤ 0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.

CORNING

ALTOS® All-Dielectric Gel-Free Cables

CORNING

Ordering Information | Contact Customer Care at 1-800-743-2671 for other options.



1 Select fiber count.
Standard offerings:
002 - 288

2 Select fiber code.
K = 62.5 μm multimode, OM1
T = 50 μm multimode, OM2
E = Single-mode, OS2 SMF-28e+®

3 Defines cable type.
U = ALTOS® Loose Tube Cable with 2.5 mm buffer tubes

4 Defines outer jacket.
4 = All-Dielectric

5 Defines fiber placement.
T = 12 fibers/buffer tube (standard)

6 Select length markings.
3 = Markings in meters
4 = Markings in feet (standard)

7 Defines tensile strength.
1 = 2700 N/600 lbf (standard)

8 Select performance option code.
30 = 62.5 μm multimode, OM1
31 = 50 μm multimode, OM2
80 = 50 μm multimode, OM3
90 = 50 μm multimode, OM4
01 = Single-mode, OS2 (Max. attenuation 0.4/0.4/0.3 dB/km)
00 = Single-mode, OS2 (Max. attenuation 0.35/0.35/0.25 dB/km)

9 Defines cable type.
D = Gel-Free Cable

10 Defines special requirements.
20 = No special requirements



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks. Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING