

## Cables



Industrial Cat. 6<sub>A</sub> cable, stranded, 8-wire, PUR  
to make up flexible connections  
(one- or two-sided assembled system cables)

IP 20	<input checked="" type="checkbox"/>	IP 65 / IP 67	<input checked="" type="checkbox"/>	PUR		Cat. 5	<input type="checkbox"/>	Cat. 6 <sub>A</sub>	<input checked="" type="checkbox"/>
-------	-------------------------------------	---------------	-------------------------------------	-----	--	--------	--------------------------	---------------------	-------------------------------------

Cable structure	4 x 2, Twisted Pair, shielded, PIMF
Core structure	4 x 2 x AWG 26/7
Wire insulation	PE, Ø 1.05 mm
Sheath material	PUR
Cable sheath diameter	6.3 mm ... 6.9 mm
Transmission performance	Category 6 <sub>A</sub> / Class E <sub>A</sub> up to 500 MHz according to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate	10/100/1000 Mbit/s, 10 Gbit/s
Shielding	Paired shielded with additional cable shield
Operating temperature range	-40 °C ... +80 °C
Standard lengths	20 m / 50 m / 100 m / 500 m
Colour	Yellow
<b>Advantages</b>	<ul style="list-style-type: none"> <li>Robust design suitable for industry</li> <li>Optimal performance reserves</li> <li>Halogen free</li> <li>RoHS compliant</li> <li>Flame retardant sheath material</li> </ul>

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Industrial Cat. 6 <sub>A</sub> cable, stranded, 8-wire PUR  20 m ring 50 m ring 100 m ring 500 m drum	09 45 600 0630 09 45 600 0640 09 45 600 0600 09 45 600 0620		
--	--	--	--