


## THW



### Product Description

Solid or stranded  
PVC insulation/jacket  
75°C, 600 V

### Applications

General purpose wiring for lighting and power in residential, commercial and industrial buildings, in accordance with NEC maximum conductor temperature of 75°C in wet or dry locations, for circuits not exceeding 600 V.

### Specifications

- CONDUCTOR: Solid or Class B stranded, annealed copper
- INSULATION: Polyvinyl Chloride (PVC)
- STANDARDS: Listed Type THW per UL 83 requirements
- AMPACITY: Based on not more than three conductors in raceway or cable or earth with an ambient temperature of 30°C and a conductor temperature of 75°C per 2008 NEC Table 310.16
- TEMPERATURE: 75°C
- VOLTAGE: 600 V

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

Unless otherwise specifically permitted in the NEC, the overcurrent protection shall not exceed 15 A for 14 AWG, 20 A for 12 AWG and 30 A for 10 AWG copper. Diameters and weights may vary among manufacturers.

Part No.	Conductor Size AWG/kcmil	No. of Strands	Insulation Thickness (in.)	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.	Amps per Conductor
6C-1401	14	Solid	0.045	0.160	22	20
6C-1201	12	Solid	0.045	0.180	30	25
6C-1001	10	Solid	0.045	0.200	44	30
6D-1401	14	7	0.045	0.170	23	20
6D-1201	12	7	0.045	0.190	32	25
6D-1001	10	7	0.045	0.210	46	30
6D-0801	8	7	0.060	0.270	68	50
6D-0601	6	7	0.060	0.310	105	65
6D-0401	4	7	0.060	0.360	160	85
6D-0301	3	7	0.060	0.390	195	100
6D-0201	2	7	0.060	0.420	245	115
6D-0101	1	19	0.080	0.490	315	130
6D-1011	1/0	19	0.080	0.530	390	150
6D-2021	2/0	19	0.080	0.580	480	175
6D-3031	3/0	19	0.080	0.630	595	200
6D-4041	4/0	19	0.080	0.690	753	230
6D-2501	250	37	0.095	0.770	880	255
6D-3001	300	37	0.095	0.820	1,040	285
6D-3501	350	37	0.095	0.870	1,205	310
6D-4001	400	37	0.095	0.920	1,365	335
6D-5001	500	37	0.095	1.010	1,685	380
6D-6001	600	61	0.110	1.120	2,030	420
6D-7501	750	61	0.110	1.220	2,510	475
6D-10001	1000	61	0.110	1.380	3,305	545

### Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.