

XHHW-2

**Product Description**

Solid or stranded
XLP insulation/jacket
90°C wet/dry
600 V

Applications

General purpose wiring for control, switchboard, lighting and power circuits in residential and commercial buildings and industrial plants, and for utility substations, meters and generating plants.

Specifications

- CONDUCTOR: Class B stranded, annealed, bare copper
- INSULATION: Cross-Linked Polyethylene (XLP)
- STANDARDS: Listed Type XHHW-2 per UL 44 Thermoset-Insulated Wires and Cables, meets construction requirements of ICEA S-95-658 (NEMA WC 70), conforms to Federal Specification A-A-59544
- AMPACITY: Based on not more than three conductors in raceway or cable or earth with an ambient temperature of 30°C per 2008 NEC Table 310.16
- TEMPERATURE: 90°C
- VOLTAGE: 600 V

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

Unless otherwise specifically permitted in the NEC, the overcurrent protection shall not exceed 15 A for 14 AWG, 20 A for 12 AWG and 30 A for 10 AWG copper. Diameters and weights may vary among manufacturers. CT rated material available in sizes 1/0 and larger.

Part No.	Conductor Size AWG/kcmil	No. of Strands	Insulation Thickness (in.)	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.	Amps per Conductor
6L-1401	14	Solid	0.030	0.130	17	25
6L-1201	12	Solid	0.030	0.150	26	30
6L-1001	10	Solid	0.030	0.170	38	40
6M-1401	14	7	0.030	0.140	18	25
6M-1201	12	7	0.030	0.160	27	30
6M-1001	10	7	0.030	0.180	40	40
6M-0801	8	7	0.045	0.240	66	55
6M-0601	6	7	0.045	0.280	96	75
6M-0401	4	7	0.045	0.320	145	95
6M-0201	2	7	0.045	0.380	225	130
6M-0101	1	7	0.055	0.440	290	150
6M-1011	1/0	19	0.055	0.480	360	170
6M-2021	2/0	19	0.055	0.520	450	195
6M-3031	3/0	19	0.055	0.580	555	225
6M-4041	4/0	19	0.055	0.630	700	260
6M-2501	250	37	0.065	0.700	830	290
6M-3001	300	37	0.065	0.750	990	320
6M-3501	350	37	0.065	0.800	1,150	350
6M-4001	400	37	0.065	0.850	1,310	380
6M-5001	500	37	0.065	0.930	1,620	430
6M-7501	750	61	0.080	1.040	2,445	535
6M-10001	1000	61	0.080	1.290	3,240	615

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.