

# FDC® Unit Connector Module, pigtailed, SC Connectors

MIC® Tight-Buffered Cable, 3 m, 6 F, Single-mode (OS2)

CORNING

Corning Cable Systems offers a variety of panels and modules for use in the FDC® unit family of products. The panels are used with field-installable connectors or in applications where the preconnectorized cables are routed directly to the FDC unit housing. Both the panels and the modules may be equipped with 900 µm single-fiber or ribbon-fiber pigtails for pigtail splicing. Panels and modules are available with a variety of connector types. Plastic modules include molded-in areas for coiling fiber slack and protecting the minimum bend-radius of the fiber.

## Features and Benefits

### Compatible with Corning Cable Systems Fiber Distribution Centers (FDC®)

Reduced inventory complexity

### Termination of interbuilding backbone cables at main or intermediate cross-connect

Variety of deployment options

### Modules accommodate various fiber and connector types

Flexibility of deployment

### Fiber routing and bend-radius protection designed into modules

Clean and easily accessible fiber routing with fewer breaks



## Specifications

General Specifications	
Application	Central Office, Carrier Networks, Enterprise Networks
Product Type	Panels & Modules
Fiber Category	Single-mode (OS2)
Cable Type Stubbed	MIC® Tight-Buffered

CORNING

# FDC® Unit Connector Module, pigtailed, SC Connectors

MIC® Tight-Buffered Cable, 3 m, 6 F, Single-mode (OS2)

CORNING

## Design - Hardware

Cable Entry Direction	Rear
Connector Configuration	SC
Connector Polish	UPC
Fiber Count	6
Housing Color	Platinum
Housing Type	FDC
Panel or Module Type	FDC

## Mechanical Characteristics

Cable Length	9.84 ft (3.0 m)
Number of Cables	1

## Design Adapter

Adapter Type	SC
--------------	----

## Ordering Information

Part Number	FDM06P06-3C-3RH000
Product Description	FDC® Unit Connector Module, pigtailed, SC connectors, MIC® Tight-Buffered Cable, 3 m, 6 F, Single-mode (OS2)

## Shipping Information

Units per Delivery	1/1
--------------------	-----

Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING