


5 kV Three Conductor Nonshielded



Product Description

Galvanized steel or interlocked aluminum armor
Nonshielded
XLP insulation
Inner and outer PVC jackets
100% or 133% insulation level

Applications

For exposed or concealed wiring in wet or dry locations. For use in ventilated, non-ventilated and ladder type cable troughs and ventilated flexible cableway in wet or dry locations. For direct earth burial.

Specifications

- CONDUCTOR: Class B stranded, bare, soft copper
- CONDUCTOR SHIELD: Cables have a semiconducting shield over the conductor
- INSULATION: Cross-Linked Polyethylene (XLP), 90 mils insulation thickness
- GROUNDING CONDUCTOR: An uninsulated Class B stranded grounding conductor is included in the cable assembly with suitable fillers
- INNER JACKET: Polyvinyl Chloride (PVC)
- ARMOR: Aluminum or galvanized steel interlocking armor
- OUTER JACKET: Polyvinyl Chloride (PVC) heat-, flame- and moisture-resistant jacket, rated -40°C, the standard color is orange but colored jackets will be provided upon request
- STANDARDS: The cable is certified to CSA C22.2 No. 131 Teck 90 cable and No. 174 for use in CSA Class 1, Division 1 hazardous locations (CSA HL rated) and passes the FT4 vertical tray flame test
- AMPACITY: Based on 90°C column of Table 2 of the 2009 Canadian Electric Code, allowable ampacities for not more than three copper conductors in raceway or cable based on 30°C ambient temperature
- TEMPERATURE: -40°C to 90°C
- VOLTAGE: 5 kV

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

After part number use: "SJ" for steel, "AJ" for aluminum, (e.g. 7TN-4043AJ). Diameters and weights may vary among manufacturers.

Part No.	Conductor Size AWG/kcmil	Ground Wire Size AWG	Nom. Diameter Inner Jacket (in.)	Nom. Diameter Armor (in.)	Nom. Diameter Outer Jacket (in.)	Approx. Wt. Alum. Armor lb./1,000 ft.	Approx. Wt. Steel Armor lb./1,000 ft.	Amps per Conductor
7TN-0803	8	10	0.94	1.14	1.23	730	1,080	50
7TN-0603	6	8	1.02	1.22	1.31	890	1,240	70
7TN-0403	4	8	1.12	1.32	1.40	1,100	1,500	90
7TN-0303	3	6	1.17	1.37	1.46	1,280	1,680	105
7TN-0203	2	6	1.24	1.44	1.52	1,440	1,740	120
7TN-0103	1	6	1.35	1.55	1.68	1,720	2,150	140
7TN-1013	1/0	6	1.43	1.63	1.76	1,980	2,500	155
7TN-2023	2/0	6	1.51	1.76	1.89	2,400	3,000	185
7TN-3033	3/0	4	1.62	1.87	2.00	2,850	3,500	210
7TN-4043	4/0	2	1.79	2.04	2.18	3,500	4,300	235
7TN-2503	250	4	1.90	2.16	2.28	3,950	4,800	270
7TN-3003	300	4	2.02	2.28	2.40	4,500	5,400	300
7TN-3503	350	3	2.12	2.362	2.52	5,200	6,100	325
7TN-4003	400	3	2.20	2.46	2.62	5,800	6,700	360
7TN-5003	500	2	2.38	2.62	2.78	6,900	7,900	405
7TN-6003	600	2	2.56	2.80	2.96	8,000	9,100	455
7TN-7503	750	2	2.76	3.00	3.18	9,600	10,800	500
7TN-10003	1000	1	3.14	3.40	3.58	12,600	14,000	585

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.