

FutureCom™ Top hat rail adapter, LANscape®

Grey

CORNING

The FutureCom™ Industrial top hat rail adapter is suitable for installation on 35 mm top hat rails. It provides a potential equalisation spring and allows due to its modular design a free configuration of each single port with FutureCom copper modules as well as LANscape® fibre optic modules.

Features

- Compact design with small dimensions
- Electrical spring contact to top hat rail (bonding, grounding)
- Inclined design with labeling field and dust protection flap
- Tool-less and fast installation on top hat rails
- Tool-less installation of module
- Top hat rail adapter light grey, RAL 7035
- Flame retardant, fire Class UL94 V-0
- Temperature range: -20°C to +70°C
- Recyclable and free of heavy metal



Part Number: WAXISE-V0103-C001

Specifications

General Specifications

Halogen-free	Yes
--------------	-----

Temperature Range

Installation and assembly	-20 °C to 70 °C
---------------------------	-----------------

Design - Hardware

Number of Ports	1
Colour	Grey

FutureCom™ Top hat rail adapter, LANscape®

Grey

CORNING

Chemical characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
Flame Retardance	Flame retardant, fire Class UL94 V-0

Ordering Information

Part Number	WAXISE-V0103-C001
Weight	16 g

Shipping Information

Units per Delivery	1/1
--------------------	-----



Corning Cable Systems GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, Germany

TEL: 00800-2676-4641 (00800-CORNING1) · FAX: +49-30-5303-2335 · www.corning.com/cablesystems/emea

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/emea/trademarks. Corning Cable Systems is ISO 9001 certified. © 2013 Corning Cable Systems. All rights reserved.