

Wall-Mountable Splice Housings (WSH)

For up to (16) 0.2-in (Type 2S, 2R or 2A) splice trays



Corning Cable Systems Wall-Mountable Splice Housing (WSH) provides storage and protection of fiber splices in individually accessible trays. The wall-mountable housing is designed to store the optical fibers being spliced within the tray and can accommodate either (16) 0.2 in (Type 2S or 2R) or (11) 0.4 in (Type 4S or 4R) splice trays.

The front door of the housing is a work surface that can support the weight of a fusion splicer and features a lip around the door to help retain loose items. Multiple cable entry/exit locations are provided on the top and bottom and grommets prevent dust from entering the housing. Depending on the entry location of the cables into the housing, the strain-relief bracket can be moved to a variety of positions. The design also includes the Corning Cable Systems Universal Cable Clamp and provisions for mounting an optional grounding kit.

The WSH can be used in conjunction with a wall-mountable connector housing (WCH) for termination. The cable entry/exit locations line up with cable entries on the WCH-12P.



Features and Benefits

- Front door can be used as a work surface**
Convenience for splicing
- Use with LANscape® Solutions WCH-12P**
System compatibility
- Provides midspan access capability**
System access
- Universal cable clamp

Specifications

General Specifications	
Application	Enterprise Networks
Mounting Type	Wall-Mountable
Product Type	Wall-Mountable Hardware

Wall-Mountable Splice Housings (WSH)

For up to (16) 0.2-in (Type 2S, 2R or 2A) splice trays

CORNING

Design - Hardware

Housing Type	WSH
Splice Tray Options	Up to (16) 0.2-in (Type 2S, 2R or 2A) splice trays

Mechanical Characteristics

Dimensions (HxWxD)	34 cm x 57 cm x 13 cm (13.5 in x 22.5 in x 5.2 in)
--------------------	--

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Ordering Information

Part Number	WSH-16SPT
Product Description	Wall-Mountable Splice Housings (WSH), for up to (16) 0.2-in (Type 2S, 2R or 2A) splice trays

Shipping Information

Units per Delivery	1/1
Package Contents	Wall-Mountable Splice Housing; installation guide; unit label; 4 nylon lock nuts, 6-32 SS; 4 wing nuts 6-32; spiral wrap (6 ft); 2 UCC strain-relief kits; 2 UCC mounting brackets; 2 strength member strain-relief kits; 2 strain-relief brackets and 12 tie wraps, 1/8 x 4-in
Shipping Weight	4.1 kg (9 lb)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING