

FutureCom™ F/FTP 450/23, blue

Category 6, 1000 m

CORNING

The FutureCom™ F/FTP 450/23 cable is designed for applications up to 450 MHz and its transmission characteristics exceed Category 6 specifications according to EN 50288-5-1, IEC 61156-5 and TIA/EIA 568.

High system margins for the complete link according to ISO/IEC 11801 (AMD 2:2010) and EN 50173 (Series) will be achieved by using corresponding hardware together with this copper data cable.

Due to the very low delay skew between the pairs these FutureCom cables are especially suitable for Gigabit Ethernet. The cable has a streamlined construction and low weight.


Each pair is individually foil shielded, which guarantees outstanding shielding characteristics. The cable satisfies Class B interference radiation standards according to EN 55022, as well as immunity according to EN 55024, which enables the realisation of CE-compatible networks.

Features

- F/FTP 450/23 cable specified up to 450 MHz
- Outstanding electrical characteristics
- Each twisted pair is shielded with metal foil (PIMF)
- Streamlined design
- Lightweight
- Low skew between the pairs
- Halogen-free (LSZH)
- Flame retardant according to IEC 60332-3-24 and EN 50266-2-4
- Non-corrosive according to IEC 60754-2 (FRNC) and EN 50267
- Low smoke according to IEC 61034 and EN 50268



Part Number: CCXDDA-D0047-C001-L7



Cross Section of Order Number: CCXDDA-D0047-C001-L7

FutureCom™ F/FTP 450/23, blue

Category 6, 1000 m

CORNING

Specifications

General Specifications

Environment	Indoor
Cable Type	F/FTP
Category	6
Bandwidth	450 MHz
Halogen-free	Yes

Temperature Range

Installation and assembly	0 °C to 50 °C
Operation	-20 °C to 60 °C

Cable Design

No. of Pairs	4
Outer jacket material	LSZH/FRNC
Outer jacket colour	Blue

Mechanical characteristics

Conductor insulation	Halogen-free foam-skin material
Min. Bend Radius Operation	≥ 22 mm (for 2x (4x2...) over flat side)
Min. Bend Radius Installation	≥ 60 mm (for 2x (4x2...) over flat side)
Copper conductor	AWG 23
Fire Load	0.57 MJ/m
Maximum Tensile Strength	101 N
Nominal Outer Diameter	7.2 mm

FutureCom™ F/FTP 450/23, blue

Category 6, 1000 m

CORNING

Electrical characteristics (at 20°C)

Largest resistance margin	1 %
Insulation resistance	> 5000 MΩ x km
Surface transfer impedance	< 100 mΩ/m at 10 MHz
Delay skew	4 ns/100 m
Coupling Attenuation	75 dB
Max. loop resistance	165 Ω/km

Electrical characteristics (at 20°C)

Frequency [MHz]*	1	10	16	20	31.25	62.5	100	250	450
Attenuation according to standard [dB/100 m]*	2.1	6.0	7.6	8.5	10.8	15.5	19.9	33.0	-
Typical attenuation [dB/100 m]*	1.8	5.3	6.8	7.6	9.6	13.6	17.3	27.7	38.0
NEXT according to standard [dB/100 m]*	66.0	59.3	56.2	54.8	51.9	47.4	44.3	38.3	-
Typical NEXT values [dB/100 m]*	100	100	100	100	100	97.0	95.0	90.0	85.0
PSNEXT according to standard [dB/100 m]*	64.0	57.3	54.2	52.8	49.9	45.4	42.3	36.3	-
Typical PSNEXT values [dB/100 m]*	98.0	98.0	98.0	98.0	98.0	95.0	93.0	88.0	83.0
ACR-F according to standard [dB/100 m]*	66.0	50.0	45.9	44.0	40.1	34.1	30.0	22.0	-
Typical ACR-F values [dB/100 m]*	93.0	93.0	93.0	93.0	90.0	86.0	83.0	70.0	54.0
PSACR-F according to standard [dB/100 m]*	64.0	47.0	43.0	41.0	37.1	31.1	27.0	19.0	-
Typical PSACR-F values [dB/100 m]*	91.0	91.0	91.0	91.0	88.0	84.0	81.0	68.0	52.0
ACR-N according to Standard [dB/100 m]*	63.9	53.3	48.6	46.3	41.1	31.9	24.4	5.3	-
Typical ACR-N values [dB/100 m]*	98.2	94.7	93.2	92.4	90.4	82.4	77.7	62.3	47.0

Chemical characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Ordering Information

Part Number	CCXDDA-D0047-C001-L7
Product Description	FutureCom™ F/FTP 450/23, 1000 m
Weight	48 kg/km
Length	1,000 m

FutureCom™ F/FTP 450/23, blue

Category 6, 1000 m

CORNING

Shipping Information

Maximum delivery length	1,000 m
Packing type	drum



Corning Cable Systems GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, Germany

TEL: 00800-2676-4641 (00800-CORNING1) · FAX: +49-30-5303-2335 · www.corning.com/cablesystems/emea

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/emea/trademarks. Corning Cable Systems is ISO 9001 certified. © 2013 Corning Cable Systems. All rights reserved.