


PowerDsine 3504G

Compact 4-port Gigabit Midspan for the enterprise market



Overview

The PowerDsine 3504G offers a cost effective, fully IEEE 802.3af compliant solution to upgrade existing infrastructures with PoE, providing a maximum of 15.4 watts of power through each port and ensuring safe operation of any standard PoE data terminal. PowerDsine PD-3504G provides PoE to IP telephones, wireless LAN access points, security network cameras and IP terminals to receive power, along with data, over standard Ethernet cables, leaving network infrastructure completely unaltered.

With the midspan's plug-and-play installation, they are easily and cost effectively implemented leveraging an existing Ethernet infrastructure while at the same time providing the assurance of a future proof network.

PD-3504G Features

- Safe & reliable power over existing Ethernet infrastructure
- Stackable and compact
- Cisco and legacy PoE support*
- Plug-and-play installation
- Guaranteed uptime

* Dongles required

PD-3504G Specifications

No. of Ports	4
Pass Through Data Rates	10/100/1000 Mbps
Power over Ethernet Output	Pin Assignment and Polarity: 4/5 (+), 7/8 (-) Output Power Voltage: 55Vdc User Port Power: 15.4 Watts
Input Power Requirements	AC Input Voltage: 100 to 240 Vac AC Input Current: 1A @110 Vac 0.4A @ 240Vac AC Frequency: 50 to 60 Hz
Dimensions	148 mm (W) x 224 mm (H) x 43 mm (L) 5.82 in. x 8.82 in. x 1.69 in
Weight	1.4 lbs (.62 kg)
Indicators	System Indicator: AC Power (Green) User Indicator: Channel Power (Green)
Connectors	Shielded RJ-45, EIA 568A and 568B
Environmental Conditions	Operating Ambient Temperature: 32° to 104°F (0°C to 40°C) Operating Humidity: Maximum 90%, Non-condensing Storage Temperature: -4° to 158°F (-20° to 70°C) Storage Humidity: Maximum 95%, Non-condensing Operating Altitude: -1000 to 10,000 ft. (-304.8 to 3048 m)
Reliability	MTBF: 300,000 hrs. @25°C
Thermal Rating	51 BTU/Hr
Warranty	1-year
Regulatory Compliance	IEEE 802.3af (PoE, PoH Type 1), RoHS Compliant, WEEE Compliant, CE
Electromagnetic Emission & Immunity	FCC Part 15, Class B EN 55022 Class B (Emissions) EN 55024 (Immunity), VCCI
Safety Approvals	UL/cUL Per EN 60950 GS Mark Per EN 60950

PD-3504G Midspan

Ordering Information

Part Number	Name	Ports
PD-3504G/AC	PowerDsine 3504G	4-port

For More Information

North America

PowerDsineUSA@microsemi.com

EMEA

(Europe, Middle East, Africa)

PowerDsine@microsemi.com

LATAM

(Latin America)

PowerDsineLATAM@microsemi.com

APAC

(Asia Pacific)

PowerDsineAPAC@microsemi.com



Microsemi®

Power Matters.

Microsemi Corporation (NASDAQ:MSCC) offers the industry's most comprehensive portfolio of semiconductor and networking technology. PowerDsine® PoE Systems, a Microsemi brand, is the thought leader in energy efficient, high power PoE technology. Learn more at microsemi.com/powerdsine

©2011 Microsemi Corporation. All rights reserved. Microsemi and the Microsemi logo are trademarks of Microsemi Corporation. All other trademarks and service marks are the property of their respective owners.

MSC-PD-DS-3504G-8.2011