

19" blank and vented panels with brush

product	code
Blank and vented panels with brush	
19" fast blank panel 1U, color black	DP-ZA-1F
19" fast blank panel 2U, color black	DP-ZA-2F
19" fast blank panel 3U, color black	DP-ZA-3F
19" fast blank panel 5U, color black	DP-ZA-5F
19" blank panel 1U, color black	DP-ZA-1U
19" blank panel 3U, color black	DP-ZA-3U
19" blank panel 5U, color black	DP-ZA-5U
19" vented panel with brush and cable management, color black	DP-BP-02
19" vented panel with double layer brush, color black	DP-BP-03
19" divided vented panel with double layer brush, color black	DP-BP-03-D

These panels are mounted to 19" vertical extrusions. Blank panels are used to cover empty positions in rack. Vented panels enable front to rear cable passage through empty positions in the rack while helping to minimize by-pass airflow.




19" fixed shelves

Fixed shelves represent the basic option for supporting equipment which is not mounted on 19" vertical extrusions. The whole surface is perforated for effective ventilation.

product	code
Fixed shelves	
19" shelf with supporting brackets, depth 250 mm	DP-PT-250
19" shelf with supporting brackets, depth 350 mm	DP-PT-350
19" shelf with supporting brackets, depth 450 mm	DP-PT-450
19" shelf with supporting brackets, depth 550 mm	DP-PT-550
19" shelf with supporting brackets, depth 650 mm	DP-PT-650
19" shelf with supporting brackets, depth 750 mm	DP-PT-750
19" shelf, depth 450 mm, load rating 100kg	DP-PZ-450
19" shelf, depth 550 mm, load rating 100kg	DP-PZ-550
19" shelf, depth 650 mm, load rating 100kg	DP-PZ-650
19" shelf, depth 750 mm, load rating 100kg	DP-PZ-750

- Made of 1.5mm sheet steel
- Supporting brackets included
- Load rating max. 20kg balanced load

(Load rating decreased to 25% when mounted only on front pair of vertical extrusions)



Color sampler:

RAL 9005

19" pull-out shelves

Pull-out shelves allow support of equipment which is not mounted on the 19" vertical extrusions. Owing to the telescopic system, the equipment can be accessed very easily. The whole surface is perforated for effective ventilation.

product	code
Pull-out shelves	
19" pull-out shelf, depth 250 mm	DP-PO-250V
19" pull-out shelf, depth 350 mm	DP-PO-350V
19" pull-out shelf, depth 450 mm	DP-PO-450V
19" pull-out shelf, depth 650 mm	DP-PO-650V

- Height 1U
- Made of 1.5mm sheet steel
- 1 pair of side telescopic rails
- Load rating max. 25kg balanced load

(Load rating decreased to 25% when mounted only on front pair of vertical extrusions)

Color sampler:

RAL 9005



19" pull-out high load shelves

- Height 1U
- Made of 2mm and 2.5mm sheet steel
- Max. pull-out 450 mm
- Load rating max. 80kg balanced load

Color sampler:

RAL 9005

product	code
Pull-out high load shelves	
19" pull-out shelf, depth 450 mm, height 1U, high-load	DP-PZ-450V
19" pull-out shelf, depth 550 mm, height 1U, high-load	DP-PZ-550V

