

Number of contacts

2



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Modul	09 14 002 3051	09 14 002 3151		
Removal tool for TC contacts in 100 A crimp module	09 99 000 0383	09 99 000 0383		

Han
Modular

Identification	Wire gauge (mm ²)	Part number		Drawing	Dimensions in mm
		Male contact	Female contact		
Crimp contacts* silver plated					
	10	09 11 000 6114	09 11 000 6214		
	16	09 11 000 6116	09 11 000 6216		
	25	09 11 000 6125	09 11 000 6225		
	35	09 11 000 6135	09 11 000 6235		

Wire gauge	∅	Stripping length (A)
10 mm ²	4.3	19 mm
16 mm ²	5.5	19 mm
25 mm ²	7.0	19 mm
35 mm ²	8.2	16 mm

for stranded wire acc. to IEC 60 228 Class 5

* Crimp zone acc. to DIN EN 46 235