



PRODUCT DATA SHEET

Controlled Document - Engineering Drive

1530 Shields Drive
 Waukegan, IL 60085
 Toll-Free (800) 323-9355
 Fax: (847) 689-1192

Seoprene® 600V SEOOW

Construction Parameters:

CONDUCTOR: 8 AWG - 2 AWG stranded bare copper per ASTM B-174
INSULATION: TPE
JACKET: TPE
COLOR: Black (Other colors available upon request)
PRINT LEGEND: CCI SEOPRENE 105 XX AWG (X.XX mm²) X/C SEOOW 600V -50C TO 105C WATER RESISTANT
 P-07-KA070025-MSHA

PHYSICAL PROPERTIES:

TEMPERATURE RANGE: -50°C to 105°C
WATER RESISTANT: Yes

ELECTRICAL PROPERTIES:

VOLTAGE RATING: 600V rms, Max

Industry Approvals:

- o MSHA
- o EPA 40 CFR, Part 26, Subpart C, heavy metals per Table 1, TCLP method

Part Number	AWG	No. Cond.	Stranding	Insulation Wall, Nom.		Jacket Wall, Nom.		O.D., Nom.		Net Weight		Amps*	Nom. DCR Ω/1M'
				Inches	mm	Inches	mm	Inches	mm	Lb./kft.	kg/km		
22220	8	2	96/28	0.048	1.22	0.090	2.29	0.657	16.69	243	362	40	0.70
22320	8	3	96/28	0.048	1.22	0.090	2.29	0.696	17.68	311	463	40	0.70
22420	8	4	96/28	0.048	1.22	0.100	2.54	0.778	19.76	402	598	35	0.70
22470	8	5	96/28	0.048	1.22	0.100	2.54	0.846	21.49	486	723	28	0.70
22221	6	2	96/26	0.048	1.22	0.090	2.29	0.747	18.97	336	500	55	0.42
22321	6	3	96/26	0.048	1.22	0.100	2.54	0.813	20.65	452	673	55	0.42
22421	6	4	96/26	0.048	1.22	0.100	2.54	0.887	22.53	575	856	45	0.42
22521	6	5	96/26	0.048	1.22	0.110	2.79	0.987	25.07	715	1064	36	0.42
22222	4	2	96/24	0.048	1.22	0.125	3.18	0.887	22.53	503	749	70	0.28
22322	4	3	96/24	0.048	1.22	0.110	2.79	0.908	23.06	625	930	70	0.28
22422	4	4	96/24	0.048	1.22	0.125	3.18	1.022	25.96	821	1222	60	0.28
22522	4	5	96/24	0.048	1.22	0.125	3.18	1.112	28.24	998	1485	48	0.28
22223	2	2	119/0.0223	0.050	1.27	0.125	3.18	1.084	27.53	712	1060	95	0.17
22323	2	3	119/0.0223	0.050	1.27	0.129	3.28	1.158	29.41	985	1466	95	0.17
22423	2	4	119/0.0223	0.050	1.27	0.125	3.18	1.260	32.00	1241	1847	80	0.17
22523	2	5	119/0.0223	0.050	1.27	0.135	3.43	1.391	35.33	1540	2292	64	0.17

Note: All dimensions & weights are nominal subject to industry standards and tolerances unless otherwise noted.

* Ampacity based on NEC Table 400.5(A) and CEC Table 12.

This product complies with European Directive 2002/95/EC (RoHS)
 The customer will accept all factory lengths and +/- 10 percent of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of product(s) is conditioned upon acceptance of a purchase order subject to Coleman disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Company Name: _____

Date: _____

Customer Approval: _____

Customer Title: _____

Specification Issue Date: June 22, 2012