



Technical Data Sheet

Anixter Part No:

A4-J03-0015-06-ARC

Description

Flexible plain annealed copper conductors, low temperature PVC insulation, cores laid up, low temperature PVC sheath (blue) "Arctic Grade" Type 3183A BS6004 : 2012 Table 6

Dimensions

Number of cores	3	no.
Nominal conductor size	1.5	mm ²
Nominal conductor stranding	30/0.25	#/mm
Insulation thickness	0.7	mm
Outer sheath thickness	0.9	mm
Minimum outer diameter	7.4	mm
Maximum outer diameter	9.4	mm

Electrical Characteristics

Nominal voltage rating (U _o /U)	300/500	Vrms
Maximum DC conductor resistance @ 20°C	13.3	ohm/km
Maximum AC conductor resistance @ 70°C	15.9	ohm/km
Reactance @ 50 Hz	0.106	ohm/km
Impedance @ 90°C, 50Hz	9.82	ohm/km
Voltage drop	32	mV/A/m
Conductor short-circuit rating (1s)	0.172	kA
Sustained Current Ratings: In air (single phase a.c.,30°C ambient temperature)	16	A

Physical Characteristics

Minimum operating temperature	-40	°C
Maximum conductor operating temperature	70	°C
Maximum conductor short-circuit temperature	160	°C
Conductor material	Flexible Class 5 plain annealed copper conductors to BS EN 60228	
Insulation material	Low temperature PVC insulation Type TI 4 to BS EN 50363-3	
Outer sheath material	Low temperature PVC sheath Type 10 to BS7655Section 4.2	
Maximum pulling tension by conductor eye	20	kgf
Minimum Bending Radius:		
Fixed installation	30	mm
Free movement (subject to flexing)	50	mm
Flame resistance	Flame retardant to BS EN 60332-1-2	
Weight	120	kg/km

Core Identification: green/yellow, blue, brown

Issue No: 1

Drawn By: M S Fordham

Date: 18/07/2013