



# PRODUCT DATA SHEET

Controlled Document - Engineering Drive

1530 Shields Drive  
Waukegan, IL 60085  
Toll-Free (800) 323-9355  
Fax: (847) 689-1192


PART NUMBER: 31606  
DESCRIPTION: 16/16 STRANDED TYPE SEOW FLEXIBLE POWER CABLE  
CONSTRUCTION: This cable consists of sixteen bare copper insulated conductors cabled with fillers and an overall jacket.  
APPROVALS: UL Standard 62, CSA 22.2 No. 49, NEC Article 400., MSHA  
APPLICATION: 600V Portable Oil and Water Resistant Submersible Outdoor Flexible Power Cable

## Construction Parameters:

Conductor	16 AWG Bare Copper
Stranding	26/30
Insulation Material	PVC
Insulation Thickness	0.031" Nom.
Insulated Conductor Diameter	0.121" Nom.
Number of Conductors	16
Lay Length	7.50" Nom.
Filler Type	Polypropylene
Separator/Wrap	Paper Tissue
Jacket Material	PVC
Jacket Thickness	0.096" Nom.
Overall Cable Diameter	0.760" Nom.
Approximate Cable Weight	356.5 Lbs/1M' Nom.
Flame Rating	UL/CSA Horizontal Flame Test

## Electrical Properties:

Temperature Rating	-50°C to 105°C
Operating Voltage	600 V RMS Max.
DC Resistance per Conductor @ 20°C	4.08 Ohms/1M' Nom.
Max Ampacity per Conductor (Per NEC Table 400-5a)	5.0 amps/cond (Assume fifteen current carrying conductors) (Note: Because of 105C temperature rating, higher current can be used under engineering supervision)

Insulation Colors	Black White Red Green Orange Blue White/Black Red/Black Green/Black Orange/Black Blue/Black Black/White Red/White Green/White Blue/White Black/Red
Jacket Color	Black (Other colors available for minimum order - consult factory)
Legend (White Surface Ink Print - MSHA in indent)	 CCI SEOPRENE 105 16 AWG (1.32mm <sup>2</sup> ) 16/C SEOW E54864 (UL) 600V -50C TO 105C CSA LL39753 STOOW(TPE) -50C TO 105C FT2 WATER RESISTANT P-241-3-MSHA

This product complies with European Directive 2002/95/EC (RoHS)

On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name \_\_\_\_\_ Date Signed \_\_\_\_\_

Customer Approval \_\_\_\_\_

Specification Issue Date: November 26, 2010