



CAN YOUR PDU PIVOT?

TRUE INNOVATION. ONLY FROM SERVER TECH.

You've never seen anything like this before. Introducing the PDU Power Pivot™, the newest patented innovation from Server Tech, inventors of the intelligent PDU. The PDU Power Pivot's incredibly flexible design with a 90 degree rotatable power cord makes it the ultimate PDU for multiple racks and multiple facilities with overhead power or raised floor.




A 90 degree user rotatable power cord simplifies PDU mounting

STV-4102: 208-240V 30A 24 IEC C13 Outlets

The Switched STV-4102 combines remote configuration and management with power distribution and environmental monitoring. Reboot a single or dual-power server with one command. Receive SNMP-based alerts and email alerts when power or environmental conditions exceed thresholds. Assign user specific access rights to designated outlets or groups.

The Switched STV-4102 uses an Auto-Flip Input Current Display. When combined with the PDU Power Pivot this provides users with the ultimate in flexibility no matter the rack or the infeed power location. Low profile UL 489 rated circuit breakers provide a shallow enclosure to help clearance and airflow in the rear of the data center cabinet.



Master

Expansion



Models

North America

Master	Expansion	Input	Input Current	Input Plug
STV-4102C	SEV-4102C	208-240 VAC, 50/60 Hz	30 A	NEMA L6-30P, 10 ft (3 m) cord

Global

Master	Expansion	Input	Input Current	Input Plug
STV-4102K	SEV-4102K	230 VAC, 50/60 Hz	32 A	IEC 60309 2P+G, 6hr (Blue), 3 m (10 ft) cord

Specifications

Input

- PIPS® Monitoring Parameters: Input current (A), voltage (V), power (kW), apparent power (VA), power consumption (W-hr), crest factor, power factor
- Meets or exceeds ANSI C12.1 for +/- 1% Billing Grade Accuracy (independently tested by UL)
- Power Pivot flexible mounting power infeed

Output

- Type: (24) IEC 60320/C13 High Retention Locking Receptacles
- Voltage: 200-240 VAC

Display

- Input Current LED
- Reversible Auto-Flip Design (Rotates with PDU)

Branch Circuit Protection

- UL489 Compliant Circuit Breakers, Double-pole, Single Throw, 20A
- 2 Branches with (12) IEC 60320/C13 Outlets

Dimensions and Weights

Model	Dimensions (LxWxD)	Shipping Dimensions (LxWxD)	Shipping Weight
S[]V-4102[]	69.0 x 1.75 x 2.25 in. (175 x 4.4 x 5.7 cm)	75 x 9 x 6 in. (191 x 22 x 14 cm)	18.5 lb. (8.4 kg)

Interface and Protocol Support

Master PDU

- 10-100 Mbps Ethernet (RJ-45 connector)
- RS-232 serial (RJ-45 connector)
- (2) temperature/humidity sensor inputs (RJ-11)
- Link port (RJ-12)
- Web browser and serial interface
- HTTP/HTTPS, SSLv3/TLSv1, SSHv2, Telnet
- SNMPv2 and v3 (TRAPS, GET, SET)
- IPv4 and IPv6
- LDAPv3/LDAPS, TACACS+, RADIUS
- (2) temperature/humidity sensor inputs (RJ-11)

Expansion PDU

- Link port (RJ-12)
- (2) temperature/humidity sensor inputs (RJ-11)



Environmental Requirements

	Operating	Storage
Temperature	32° to 140° F (0° to 60° C)	-40° to 185° F (-40° to 85° C)
Relative Humidity	8% to 90% non-condensing	8% to 90% non-condensing
Elevation (above MSL)	0 to 10,000 ft (0 to 3047 m)	0 to 50,000 ft (0 to 15239 m)

Certifications

North America

- cTUVus Mark to UL 60950-1: 2007 and CAN/CSA 22.2 No. 60950-1-07
- FCC Class A, Part 15
- EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

Global

- TUVGS Mark to EN 60950-1: 2006 + A11
- FCC Class A, Part 15
- EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A
- CE Mark
- RoHS/WEEE

Warranty

2 years



Locking Power Cord Options

UL Rated

Plug	Plug Type*	Connector	Length, ft (m)	Part Number
C14	Straight	C13	1.5 (0.45)	CAB-S1413-CA
C14	Straight	C13	3.0 (0.91)	CAB-S1413-FA
C14	Straight	C13	6.0 (1.82)	CAB-S1413-NA
C14	Straight	C19	6.0 (1.82)	CAB-S1419-NA
C14	Left Angle	C13	1.0 (0.30)	CAB-1506A
C14	Left Angle	C13	1.5 (0.45)	CAB-L1413-CA
C14	Left Angle	C13	2.0 (0.61)	CAB-L1413-DA
C14	Left Angle	C13	4.0 (1.21)	CAB-1506G

* Note: the bend of the angled cords is referenced with the ground pin at the top



Server Technology

HEADQUARTERS - NORTH AMERICA

Server Technology, Inc.
1040 Sandhill Drive
Reno, NV 89521
United States
1.775.284.2000 Tel
1.775.284.2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

U.K. Office Western Europe, Middle East and Africa

Fountain Court
2 Victoria Square
Victoria Street
St. Albans
AL1 3TF
United Kingdom
+44 (0) 1727 884676 Tel
+44 (0) 1727 220815 Fax
salesint@servertech.com



Central Europe, Eastern Europe and Russia

Niederlassung Deutschland
Server Technology LLC
42119 Wuppertal
Germany
Tel: + 49 202 693917 x 0
Fax: + 49 202 693917-10
Mobile: + 49 152 22 76 76 22
salesint@servertech.com




Server Technology


Quality Rack Power Solutions




MOUNTING BRACKET POSITIONING OPTIONS




OPTION A - MB-0005-IPT7



OPTION B - MB-0005-IPT7



OPTION C - MB-0005-IPT7



OPTION D - MB-0005-IPT7

