



Circuit diagram




Maximum power
Rated power (PHC)
Sound pressure level at 6 W/1 W
(at 1 kHz, 1 m)
Effective frequency range (-10 dB)
Opening angle
(at 1 kHz/4 kHz, -6 dB)
Rated voltage
Rated impedance
Ambient temperature range
Safety
Ball-proof
Connection
Dimensions (dia. x max. depth)
Mounting cut-out dia.
Colour
Weight
Dimensions (dia. x max. depth)
Colour
Weight
LBC 3087/41
9 W
6 W (6 - 3 - 1.5 - 0.75 W)
97/89 dB (SPL)
80 Hz to 18 kHz
160°/65°
100 V
1667 Ω
-25 to +55 °C (-13 to 131 °F)
acc. to EN 60065
acc. to DIN 18032-3
3-pole screw connector
199 x 70.5 mm (7.8 x 2.8 in)
165 mm (6.5 in)
White (RAL 9010)
720 g (1.6 lb)
LBC 3080/01
147 x 87 mm (5.8 x 3.4 in)
White (RAL 9010)
360 g (0.8 lb)

TECHNICAL PERFORMANCE DATA ACC. TO IEC 268-5

Polar diagram (measured with pink noise)



Frequency response





Loudspeakers



Instructions for use
EN | LBC 3087/41

Mounting



Connection

