

CCHE Panel, ST® Compatible

12 fibres, single-mode (OS2)



The panels are used with field-installable connectors or in applications where the pre-connectorised cables are routed directly from the equipment to the piece of inter-connect hardware. This provides an efficient way to securely mate two or more connectors.

Closet Connector Housing Panels are offered in 6-, 8-, 12-, 16- and 24-fiber panels for use with the LANscape® Solutions hardware products. The panels are used with field-installable connectors or in applications where the pre-connectorised cables are routed directly from the equipment to the inter-connect hardware. The panels are available with a variety of industry-standard adapter types. In most applications, the Closet Connector Housing Panels are designed for applications where specified labelling and connector identification are required. This is accomplished by the use of coloured icons with different symbols molded into the icon.

Features and Benefits

- Designed to accommodate all industry-standard adapter types
- Unique colour-coded connector labeling system
- Universal approach is used; one panel size fits in all standard LANscape® Solutions hardware
- Available in 6-, 8- and 12-fibre count options in most adapter styles; 16- and 24-fibre count options available in MT-RJ and LC duplex styles
- Also available for copper modules 12-fibre ST® Compatible Connector Panel, 12-fibre SC Duplex Panel, 24-fibre MT-RJ Connector Panel; 36-, 72- and 144-fibre count options available only with MTP® adapters

Specifications

General Specifications	
Fibre Category	SM (OS2)



CCHE Panel, ST® Compatible

12 fibres, single-mode (OS2)

CORNING

Design - Hardware

Housing Material	High-grade steel
Fibre Count	12
Number of Adapters	12
Colour	Black
Connector Type A	ST® Compatible

Mechanical characteristics

Dimensions (L x W)	155 mm x 35 mm
Weight	0.14 kg

Design Adapter

Adapter Type	ST® Compatible
Adapter Housing Material	Threaded metal
Adapter Housing Color	Metal
Insert Material	Ceramic
Keyed adapter	No
Shuttered adapter	No

Ordering Information

Part Number	CCHE-CP12-19
Product Description	CCHE Panel, black, 12 ST® Compatible, metal OS2

Shipping Information

Packing dimensions (L x W x H)	190 mm x 180 mm x 250 mm
Shipping Weight	0.39 kg
Units per Delivery	1/1

CCHE Panel, ST® Compatible

12 fibres, single-mode (OS2)

The Corning logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

Notes



Corning Cable Systems GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, Germany

TEL: 00800-2676-4641 (00800-CORNING1) · FAX: +49-30-5303-2335 · www.corning.com/cablesystems/emea

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/emea/trademarks. Corning Cable Systems is ISO 9001 certified. © 2013 Corning Cable Systems. All rights reserved.