

**AV5455DN-F** 5-megapixel H.264 Day/Night IP Flush In-Ceiling MicroDome™ Camera with 4mm Lens and Integrated Microphone***Bid-Spec***

---

**1.0 Description**

The AV5455DN-F MicroDome™ 5-megapixel network camera is part of Arecont Vision's full line of H.264 MicroDome™ cameras. This fully-compliant implementation of H.264 (MPEG-4, Part 10) provides full 2592 (H) x 1944 (V) megapixel resolution at full video frame rates of 14 frames per second (fps). The AV5455DN-F camera provides an all-in-one indoor flush, in-ceiling mount solution with an integrated 5-megapixel camera and a 4mm IR corrected lens. With the features of PSIA and ONVIF conformance, privacy masking, extended motion detection and flexible cropping, the AV5455DN-F is a high sensitive, PoE (IEEE 802.3af) compliant camera with a true day/night IR cut filter. Built with Arecont Vision's massively-parallel MegaVideo® processing technology, this camera offers more than 4-times the resolution of standard resolution IP cameras with the ability to output full real-time frame rates and deliver high-quality megapixel imaging.

**2.0 Bid Specification**

- The camera shall utilize a high sensitivity 5-megapixel CMOS sensor with 1/2.5" optical format.
- The camera shall have an integrated 4mm M12 mount, megapixel, IR corrected, fixed focal lens with 1/2.5" optical format, F1.6 and horizontal field-of-view of 90°.
- The camera shall have dual standard compression support with simultaneous streaming of both H.264 and MJPEG formats.
- The camera shall be fully conformant with PSIA and ONVIF industry-standards and pass conformance tests.
- The camera shall have privacy masking, the ability to select multiple regions of an arbitrary shape to block the video.
- The camera shall have an integrated microphone.
- The camera shall have an extended motion detection grid, a higher-granularity grid of 1944 distinct motion detection. The user can select between 64-zone-based motion detection and extended motion detection to provide backward compatibility with the existing Video Management System (VMS) integration.
- The camera shall have multi-streaming support of up to 8 non-identical concurrent streams (different frame rate, bitrate, resolution, quality and compression format).
- The camera shall be able to be cropped to any resolution divisible by 2 and maintain H.264 compression. It shall be possible to crop the camera to output a variety of lower resolution images.
- The camera shall output at a maximum resolution of 2592(H) x 1944(V) pixels at a maximum frame rate of 14fps.
- The camera shall feature streaming of the full field-of-view (FOV) and simultaneous multiple regions of interest (ROI) for forensic zooming.
- The camera shall be equipped with a 100Mbps LAN connector.
- The camera's shutter speed shall be 1ms - 500ms.
- The camera shall provide 21 levels of compression quality for optimal viewing and archiving.
- The camera shall support at minimum RTSP, RTP over TCP, RTP over UDP (Unicast/Multicast), HTTP1.0, HTTP1.1, DHCP, and TFTP network protocols.
- The camera shall have Real Time Streaming Protocol (RTSP) support allowing for compatibility with media players such as Apple QuickTime®, VLC Player and others.

- The camera shall feature automatic exposure, automatic multi-matrix white balance, shutter speed control, 50/60Hz selectable flicker control, programmable brightness, saturation, gamma, sharpness, windowing and decimation, simultaneous delivery of full-field view and zoomed images at video frame rate, instantaneous electronic zoom, pan and tilt, and electronic image rotation by 180°.
- The camera shall incorporate necessary algorithms and circuits to detect motion in low-light with clarity.
- It shall be possible to program the camera at binned mode to output a variety of lower resolution image and increase frame rate, i.e. 1286(H) x 972(V) pixels at 34 FPS, or 1280(H) x 800(V) pixels at 41 FPS.
- The camera shall support an IR sensitive minimum illumination of 0 Lux in black and white (B/W) mode with an additional IR light source.
- The camera's power source shall be Power over Ethernet (PoE) complying with the IEEE 802.3af standard and provide at least 5.1W of power.
- The camera shall be utilized for indoor use only.
- The camera's operating ambient temperature is -5°C (23 °F) to 50°C (122°F); stable image temperature is 0°C (32 °F) to +50°C (122 °F); storage temperature -20°C (-4 °F) to +60°C (140 °F).
- The camera shall be compliant with EMI, EMC and safety requirements, following European Standards EN55022 (Class A limits), EN55024 (IEC 61000-4-2, IEC 61000-4-3, IEC 61000-4-4, IEC 61000-4-5, IEC 61000-4-6, IEC 61000-4-8, IEC 61000-4-11), EN61000-3-2 and EN61000-3-3, EN60950-1.
- The camera shall be compliant with RoHS Directive 2011/65/EU.
- The camera shall be compliant with REACH Directive EC1907/2006.
- The camera shall be compliant with FTC "Made in USA" standard.
- The camera shall have CE mark and be UL listed.
- The camera shall have installed dimensions of:
  - 2" (52mm) Bubble ( 4" (100mm) Cover) x 1.5" (38mm) H
- The camera shall weigh 1.2lb (0.58kg).

## Quick-Spec \_\_\_\_\_

### 3.0 Minimum Performance Specification

Megapixel camera must meet the following operating requirements

#### Operational

Imaging	5-megapixel CMOS image sensor Optical format: 1/2.5"
Active Pixel Count	2592(H) x 1944(V) pixel array
Minimum illumination	Day/Night: 0 Lux, IR sensitive
Dynamic range	70.1 dB
Maximum SNR	45 dB

#### Full Field-of-View (FOV) Resolutions

2592x1944 (HxW) 1.3 megapixel

1296x972 (HxW) 1/4 resolution

#### Cropped Field-of-View Resolutions

Flexible Cropping: Crop to any resolution that is divisible by 2 pixels in H.264 and 1 pixel in MJPEG up to the maximum resolution of the camera. Example resolutions include but are not limited to the following:

2048x1536 3 MP

1920x1200 WUXGA

## A&amp;E Specifications

Rev 1.1

1920x1080 HDTV-1080p  
1600x1200 2 MP  
1280x1024 1.3 MP  
1280x720 HDTV - 720p  
1024x768 XGA  
800x600 SVGA  
704x570 PAL  
704x480 NTSC  
640x480 VGA  
352x288 CIF  
320x240 SIF

**Data Transmission**

Video frame rate up to

14fps @ 2592x1944  
16fps @ 2560x1600  
21fps @ 2048x1536  
29fps @ 1920x1080  
31fps @ 1600x1200  
41fps @ 1280x1024

In Binned Mode up to:

34fps @ 1286x972  
41fps @ 1280x800  
46fps @ 1024x768  
64fps @ 800x600  
64fps @ 860x540  
64fps @ 640x512

Compression type

H.264 (MPEG-4, Part 10)  
Motion JPEG (MJPEG)  
21 levels of quality

Transmission protocols

RTSP, RTP/TCP, RTP/UDP (Unicast/Multicast), HTTP1.0, HTTP1.1, DHCP, TFTP  
100 Base-T Ethernet Network Interface

Multi-streaming: 8 non-identical streams

**Programmability**

Binned mode

Flexible Cropping

Privacy Masking

Low-Light Noise Filter Control

Bit-Rate and Bandwidth Limitation Control

On-camera real-time motion detection with 1024 detection zones or 64 detection zones

Auto Backlight Compensation

Auto Multi-Matrix White Balance

50/60Hz Selectable Flicker Control

Electronic Pan, Tilt, Zoom (PTZ)

Electronic Image Flip – 180-Degree Rotation

Resolution Windowing Down to 1x1 Pixels for MJPEG and 2x2 Pixels for H.264

Programmable Shutter Speeds to Minimize Motion Blur

MoonLight™ Mode - Extended Exposure and Proprietary Noise Cancellation

Programmable Resolution, Brightness, Saturation, Gamma, Sharpness, Tint

Picture-In-Picture: Simultaneous Delivery of Full Field of View and Zoomed Images

Bandwidth and Storage Savings by Running at 1/4 Resolution

### **Electrical**

General purpose opto-coupled input and output

Power over Ethernet (PoE): PoE 802.3af for camera

Power consumption: 5.1 Watts maximum

### **Mechanical**

Casing:

- Die-cast aluminum case w/ plastic bracket
- Polycarbonate bubble with die-cast aluminum cover

In-ceiling mount using spring arm retention

Easy 2-axis camera adjustment w/359° pan and 88° tilt

Total Unit Dimensions:

- 2" (52mm) Bubble ( 4" (100mm) Cover) x 1.5" (38mm) H Installed (3" H total)

Weight: 1.2lbs (0.58kg)

### **Environmental**

Operating temperature -5°C (23 °F) to +50°C (122 °F)

Stable image temperature 0°C (32 °F) to +50°C (122 °F)

Storage temperature -20°C (-4 °F) to +60°C (140 °F)

Humidity 0% to 90% (non-condensing)

### **Compliance Information**

Class A FCC, Part 15; EN55022 Class A, EN55024, EN61000-3-2 and EN61000-3-3, EN60950-1

RoHS, REACH, CE Mark, UL Listed

### **Industry Standard**

PSIA and ONVIF Conformance

### **Lenses:**

4mm, F1.6, H-FOV: 90°

### **Related Documentation**

AV5455DN-F Camera Specification

Installation Manual

### **4.0 Model Numbers**

The camera shall be Arecont Vision model AV5455DN-F, 5-megapixel H.264 day/night IP MicroDome™ camera with integrated microphone and 4mm lens.

**5.0 Warranty**

Limited 3-Year Parts and Labor

*Arecont Vision reserves the right to change products or specifications without notice.*