


CADDY® CAT HP J-Hook Tree, Wall Mount – CAT32HPSWM3 (181027)



- Ideal for attaching to concrete, steel or wood surfaces
- Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic
- Ready to use out of the box, saving installation time and labor
- Requires no screws, rivets or special tools for assembly
- Provides superior fill capacity and load rating over most other non-continuous cable support alternatives
- Meets ISO®/IECSM 14763-2, TIASM 568-C and TIASM 569-C



Part Number	CAT32HPSWM3
Article Number	181027
Material	Steel
Finish	Pre-galvanized
Type	Single Sided
Diameter (Ø)	2" 50 mm
Tiers	3
Height (H)	19 1/2" 495.3 mm
Depth (D)	3 3/8" 86.4 mm
Width (W)	2" 50 mm
Hole Size (HS)	1/4" 6.5 mm
Static Load (F)	180 lb 800 N



Part Number	CAT32HPSWM3
Standard Packaging Quantity	5 pc
UPC	78285679919
UNSPSC	39131709
Approvals	cULus®

Static loads represent maximum load limit of J-Hook tree. Static load limit of each J-Hook is 60 lb (270 N).

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIASM 569-C.9.7.

cULus is a registered certification mark of UL LLC. IEC is a registered service mark of Independent Electrical Contractors, Inc. ISO is a registered trademark of International Organization for Standardization. TIA is a registered service mark of the Telecommunications Industry Association.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright © 2013 ERICO International Corporation. All rights reserved.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

