



CADDY® ROD LOCK Beam Clamp – CRLB37EG



- Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly locking it into position
- Works with slightly damaged threads and minor burrs on the threaded rod
- Reduces installation time up to 60%



Part Number	CRLB37EG
Material	Cast iron
Finish	Electro-galvanized
Rod Size (RS)	3/8" 3/8"
Flange Thickness (FT)	1/8" – 3/8" 3 – 10 mm
Height (H)	1 3/16" 30 mm
Length (L)	2.06" 52.3 mm
Width (W)	1" 25.3 mm
A	0.98" 24.9 mm
Static Load 1 (F1)	250 lb 1,100 N
Static Load 2 (F2)	500 lb 2,200 N
NB/DN	50 mm Max
Pipe Size	4" Max
Standard Packaging Quantity	25 pc
UPC	78285664943



Part Number	CRLB37EG
UNSPSC	31162905
ETIM	EC000464
Approvals	cULus FM

Static Load 1 represents 1/8" to 3/16" (3 mm to 5 mm) flange thickness. Static Load 2 represents 1/4" to 3/8" (6 mm to 10 mm) flange thickness.

For use on plain and electro zinc plated hardware only.

Recognizing that torque wrenches are generally not used or available on many job sites, the setscrew should be tightened so it contacts the I-beam and then an additional 1/2 turn added.

cULus is a registered certification mark of UL LLC. FM is a registered certification mark of FM Approvals LLC, LTD.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright © 2013 ERICO International Corporation. All rights reserved.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

