

## 15 kV Three Conductor 100% Insulation Level



### Product Description

Galvanized steel or interlocked aluminum armor  
Shielded  
XLP insulation  
Inner and outer PVC jackets  
100% insulation level

### Applications

For exposed or concealed wiring in wet or dry locations. For use in ventilated, non-ventilated and ladder type cable troughs and ventilated flexible cableway in wet or dry locations. For direct earth burial.

### Specifications

- CONDUCTOR: Class B stranded, bare, soft copper
- CONDUCTOR SHIELD: Cables have a semiconducting shield over the conductor
- INSULATION: Cross-Linked Polyethylene (XLP), 175 mils insulation thickness
- IDENTIFICATION: The insulated conductors are identified by means of a colored tape (black, red and blue) placed longitudinally immediately under the copper tape shield
- INSULATION SHIELD: Consists of a semiconducting thermosetting layer plus an overlaying metallic component, in multiconductor cables the metallic component is a helically applied lapped copper tape
- GROUNDING CONDUCTOR: An uninsulated Class B stranded grounding conductor is included in the cable assembly with suitable fillers
- INNER JACKET: Polyvinyl Chloride (PVC)
- ARMOR: Aluminum or galvanized steel interlocking armor
- OUTER JACKET: Polyvinyl Chloride (PVC) heat-, flame- and moisture-resistant jacket, rated -40°C, the standard color is red but colored jackets are available on request
- STANDARDS: The cable is certified to CSA C22.2 No. 131 and No. 174 for use in CSA Class 1, Division 1 hazardous locations (CSA HL rated) and CSA C68.3 and passes the FT4 vertical tray flame test
- AMPACITY: Refer to IEEE 835-1994 tables for ampacity values, and the Canadian Electrical Code for correction factors
- TEMPERATURE: -40°C to 90°C
- VOLTAGE: 15 kV

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • [anixter.com](http://anixter.com)

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

After part number use; "SJ" for steel, "AJ" for aluminum, (e.g. 7TP-2023AJ). Diameters and weights may vary among manufacturers.

Part No.	Conductor Size AWG/kcmil	Ground Wire Size AWG	Nom. Diameter Inner Jacket (in.)	Nom. Diameter Armor (in.)	Nom. Diameter Outer Jacket (in.)	Approx. Wt. Alum. Armor lb./1,000 ft.	Approx. Wt. Steel Armor lb./1,000 ft.	3M Terminations
7TP-0203	2	6	1.84	2.09	2.19	2,400	3,250	034004
7TP-0103	1	6	1.91	2.16	2.26	2,650	3,500	034004
7TP-1013	1/0	6	2.00	2.26	2.34	3,950	3,850	034004
7TP-2023	2/0	6	2.10	2.34	2.45	3,400	4,350	037023
7TP-3033	3/0	4	2.20	2.46	2.56	3,900	4,900	037023
7TP-4043	4/0	4	2.32	2.56	2.67	4,450	5,500	037023
7TP-2503	250	4	2.42	2.66	2.80	4,950	6,000	037023
7TP-3003	300	4	2.52	2.78	2.92	5,600	6,700	037023
7TP-3503	350	3	2.62	2.88	3.02	6,200	7,300	037023
7TP-4003	400	3	2.72	2.96	3.12	6,800	7,900	037023
7TP-5003	500	2	2.94	3.20	3.34	8,200	9,500	037023
7TP-6003	600	2	3.14	3.40	3.65	9,400	10,800	037023
7TP-7503	750	2	3.34	3.60	3.87	12,000	12,400	057312
7TP-10003	1000	1	3.68	3.92	4.22	14,000	15,400	057312

## Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • [anixter.com](http://anixter.com)

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.