


### TYPE GD

#### CABLE TO ROD/TUBE GROUND CONNECTOR

For Two Copper Cables  
to Rod or Tube



E-32

High copper alloy ground connector for joining a range of two parallel cables to rod or pipe. Especially good for grounding fence posts. High copper alloy cast body with DURIIUM™ U-bolts, nuts, and lockwashers make the GD suitable for burial in ground or concrete. One-wrench installation. UL467 Listed. Acceptable for direct burial in earth or concrete.



Catalog Number	Conductor			H	J	W	
	Tube I.P.S.	Rod Size or O.D. Range	Cable				
GD1526	1	1-1/8 - 1-1/4	4 Sol. - 2/0 Str.	3-3/8	3/8	2-5/8	
GD1529			2/0 Sol. - 250				
GD1626	1-1/4	1-3/8 - 1-1/2	4 Sol. - 2/0 Str.	3-1/2		3/8	3
GD1629			2/0 Sol. - 250				
GD174C	1-1/2	1-5/8 - 1-7/8	8 Sol. - 4 Str.	4		1/2	3-1/4
GD1726			4 Sol. - 2/0 Str.				
GD1729			2/0 Sol. - 250				
GD1734			300 - 500				
GD184C	2	2 - 2-3/8	8 Sol. - 4 Str.	4-3/8	3/8	3-3/4	
GD1826			4 Sol. - 2/0 Str.				
GD1829			2/0 Sol. - 250				
GD1834			300 - 500				
GD194C	2-1/2	2-1/2 - 2-7/8	8 Sol. - 4 Str.	5	3/8	4-1/4	
GD1926			4 Sol. - 2/0 Str.				
GD1929			2/0 Sol. - 250				
GD1934			300 - 500				
GD204C	3	3 - 3-1/2	8 Sol. - 4 Str.	5-5/8	3/8	4-7/8	
GD2026			4 Sol. - 2/0 Str.				
GD2029			2/0 Sol. - 250				
GD2034			300 - 500				
GD214C	3-1/2	3-1/2 - 4	8 Sol. - 4 Str.	6-3/8	1/2	5-1/4	
GD2126			4 Sol. - 2/0 Str.				
GD2129			2/0 Sol. - 250				
GD2134			300 - 500				
GD224C	4	4 - 4-1/2	8 Sol. - 4 Str.	6-3/8	3/8	5-7/8	
GD2226			4 Sol. - 2/0 Str.				
GD2229			2/0 Sol. - 250				
GD2234			300 - 500				

Complies with NFPA 78-86 HEAVY DUTY stacks.  
(Order: LD for lead plating for HEAVY DUTY stack applications.)

Blue highlighted items are industry standard and most frequently ordered.