


3321 (0.030 in. Wall, 600 V)



Product Description

XLPE insulation
Stranded or solid conductor
UL AWM
CSA AWM

Applications

Internal wiring of electrical and electronic appliances.

Specifications

- CONDUCTOR: Tinned copper
- INSULATION: Cross-Linked Polyethylene (XLPE), chemical
- STANDARDS: UL recognized AWM Style 3321 per UL 758 requirements.
CSA Type CL 1503 and AWM I A/B
- TEMPERATURE RATING: 150°C
- VOLTAGE RATING: 600 V

All part numbers require color code designation. Solid colors with extruded parallel stripes available.

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

Part No.	Conductor AWG	Stranding No. x AWG	Wire O.D.	Approx. Wt. lb./1,000 ft.
3321-22/7-XX	22	7x30	0.094	5.5
3321-20/10-XX	20	10x30	0.102	7
3321-18/16-XX	18	16x30	0.113	9.9
3321-16/26-XX	16	26x30	0.123	13.7
3321-14/41-XX	14	41x30	0.138	19.4
3321-12/65-XX	12	65x30	0.160	28.3
3321-10/105-XX	10	105x30	0.185	43

Insulation Color Code Chart

0.....black
 1.....brown
 2.....red
 3.....orange
 4.....yellow
 5.....green
 6.....blue
 7.....violet/purple
 8.....gray
 9.....white
 P.....pink
 T.....tan
 D.....dark (i.e. D6=dark blue)
 L.....light (i.e. L6=light blue)

For white with black stripe - 90
 For green with yellow stripe - 54
 For white with a black and red stripe - 902
 For white and black twisted conductor - 9/0
 For white, black and red twisted conductors - 9/0/2

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.