

Military Specification UNIRAP™ Cable Ties

The BURNDY® cable ties shown below meet the requirements of SAE AS23190A (formerly MIL-S-23190) in accordance with specification MS3367, MS3368, and QPL-23190.

Natural Cable Ties

Mil Spec	Distributor Pack Catalog Number	Bulk Pack Catalog Number	Description (Bundle Dia. - Tensile Strength)
MS3367-1-9	CT50175C	CT50175M	1.75" - 50 lbs.
MS3367-2-9	CT50400C	CT50400M	4" - 50 lbs.
MS3367-3-9	CT120400L	CT120400D	4" - 120 lbs.
MS3367-3-9	CT175400Q	N/A	4" - 175 lbs.
MS3367-3-9	CT175600Q	N/A	6" - 175 lbs.
MS3367-4-9	CT18075C	CT18075M	.75" - 18 lbs.
MS3367-5-9	CT30125C	CT30125M	1.25" - 30 lbs.
MS3367-6-9	CT120900L	CT120900D	9" - 120 lbs.
MS3367-6-9	CT175900Q	N/A	9" - 175 lbs.
MS3367-7-9	CT50300C	CT50300M	3" - 50 lbs.

G-5

UV Resistant Black Cable Ties

Mil Spec	Distributor Pack Catalog Number	Bulk Pack Catalog Number	Description (Bundle Dia. - Tensile Strength)
MS3367-1-0	CT50175C00	CT50175M00	1.75" - 50 lbs.
MS3367-2-0	CT50400C00	CT50400M00	4" - 50 lbs.
MS3367-3-0	CT120400L00	CT120400D00	4" - 120 lbs.
MS3367-3-0	N/A	N/A	4" - 175 lbs.
MS3367-3-0	CT175600Q00	N/A	6" - 175 lbs.
MS3367-4-0	CT18075C00	CT18075M00	.75" - 18 lbs.
MS3367-5-0	CT30125C00	CT30125M00	1.25" - 30 lbs.
MS3367-6-0	CT120900L00	CT120900D00	9" - 120 lbs.
MS3367-6-0	CT175900Q00	N/A	9" - 175 lbs.
MS3367-7-0	CT50300C00	CT50300M00	3" - 50 lbs.

Natural Identification Cable Ties


Mil Spec	Distributor Pack Catalog Number	Bulk Pack Catalog Number	Description (Bundle Dia. - Tensile Strength)
MS3368-1-A	CT50175IDC	N/A	1.75" - 50 lbs.
MS3368-2-A	CT50400IDC	N/A	4" - 50 lbs.
MS3368-3-C	CT50175ID2L	N/A	1.75" - 50 lbs. Double Strap
MS3368-4-D	CT50175ID3L	N/A	1.75" - 50 lbs. Triple Strap
MS3368-5-E	CT18075IDC	N/A	.75" - 18 lbs.

Blue highlighted items are industry standard and most frequently ordered.

UNIRAP™

IDENTIFICATION CABLE TIES


Identification cable ties are used in both bundling and identifying wire groups at the same time.



Standard Package Catalog Number	Material	Fig. No.	Marking Pad Size Inches [mm]	Maximum Bundle Diameter Inches [mm]	Minimum Tensile Strength Lbs. (N)	Length Inches [mm]	Width Inches [mm]	Installation Tool & (Setting)
CT18075IDC	Natural Nylon 6/6	1	1 × 19/64 [25.4 × 7.5]	.75 [19]	18 (80)	4.00 [102]	.10 [2.5]	MK7 (MIN)
CT18075FLC		2	13/16 × 5/16 [20.5 × 7.9]			4.25 [108]		
CT50175IDC		3	1 × 7/16 [25.4 × 11.1]					
CT50175ID2L		4	1-11/16 × 5/16 [29.8 × 23.8]	1.75 [44]	50 (222)	8.00 [203]	.18 [4.6]	MK7 (STD)
CT50175ID3L		5	1-13/16 × 15/16 [46 × 23.8]					
CT50400IDC		6	1/2 × 2-1/8 [12.7 × 54]			15.00 [381]		

UNIRAP™

MOUNTING HOLE CABLE TIES



Standard Package Catalog Number	Material	Screw Size	Maximum Bundle Diameter Inches [mm]	Minimum Tensile Strength Lbs. (N)	Length Inches [mm]	Width Inches [mm]	Installation Tool & (Setting)	Bulk Package Catalog Number
CT18075MH4C	Natural Nylon 6/6	#4 (M2.5)	.75 [19]	18 (80)	4.25 [108]	.10 [2.5]	MK7 (MIN)	CT18075MH4M
CT18075MH4C0	Black Nylon 6/6 UV							—
CT30125MH8C	Nylon 6/6	#8 (M4)	1.25 [32]	30 (133)	6.25 [159]	.14 [3.6]	MK7 (INT)	—
CT30125MH8C0	Nylon 6/6 UV							—
CT50175MH10C	Nylon 6/6	#10 (M5)	1.75 [44]	50 (222)	8.50 [216]	.18 [4.6]	MK7 (STD)	CT50175MH10M
CT50175MH10C0	Nylon 6/6 UV							CT50175MH10M0
CT50400MH10C	Nylon 6/6 GP							—
CT50400MH10C0	Nylon 6/6 UV	1/4" (M6)	4.00 [102]	50 (222)	16.00 [406]		MK9 (STD)	CT50400MH10M0
CT120400MH14L	Nylon 6/6							—
CT120400MH14L0	Nylon 6/6 UV							CT120400MH14D0

Blue highlighted items are industry standard and most frequently ordered.