



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PDUH20HVL6

Single-Phase Basic PDU, 20A 208/240V, 1U Horizontal Rackmount, 2 C19 and 12 C13 outlets, NEMA L6-20P input plug

Highlights

- Basic single phase 20A 208/240V PDU
- 1U horizontal rackmount installation
- L6-20P input; 15 ft. / 4.5m line cord
- 2 C19 and 12 C13 outlets
- Reversible housing; 3.75 in. / 9.5cm depth



Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Applications

- Ideal for datacenters, network closets, equipment racks and a wide variety of other application types

Package Includes

- PDUH20HVL6 PDU rackmount PDU
- Owner's manual

Features

- 20A single phase 208/240V Basic Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- Attached NEMA L6-20P input
- 14 outlets (2 C19, 12 C13)
- 15 ft. / 4.5m line cord
- 1U horizontal rackmount format installs in one rack space
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Reversible housing
- Back panel grounding lug

Specifications

OVERVIEW	
PDU Type	Basic
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output nominal voltage	208/240V

Overload protection	n/a
Outlet quantity / type	2 C19, 12 C13
Outlet Type	IEC-C13, IEC-C19
INPUT	
Nominal Input Voltage(s) Supported	208V AC; 240V AC
PDU Input Voltage	208; 240
Maximum Input Amps (A)	20
Maximum Input Amps (A) Details	20A maximum (Agency de-rated to 16A continuous)
PDU Plug Type	NEMA L6-20P
Input cord length (ft.)	15
Input cord length (m)	4.5
Input cord details	Input cable is attached
Voltage compatibility (VAC)	208/240
Phase	Single-Phase
PHYSICAL	
Shipping Dimensions (HWD/in)	2.25 x 20.5 x 9.5
Shipping Dimensions (HWD/cm)	5.7 x 52.1 x 24.1
Shipping weight (lbs)	5.9
Shipping weight (kg)	2.7
Unit Dimensions (HWD/in)	1.75 (1U) x 17.25 x 3.75
Unit Dimensions (HWD/cm)	4.45 x 43.8 x 9.5
Unit weight (lbs)	3.75
Unit weight (kg)	1.7
Material of construction	Sheet Metal
Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
Form factors supported	1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation
PDU Form Factor	Horizontal (1U, 2U, etc)
Outlets center to center measurement	Distance between front (C13) outlets = 28.75mm; Distance between rear (C19) outlets = 55mm; Distance between rear (C13) outlets = 28.75mm
SPECIAL FEATURES	
Appearance	All black color scheme
TVSS grounding	Rear grounding lug
CERTIFICATIONS	

Certifications	Tested to UL 60950 (USA), CSA (Canada), RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
PDU\$IDE\$BRKT	Enables Vertical Installation of Select 1U PDUs, Power Strips and Surge Suppressors in SmartRack Configurations	1
P004-002-13LA	AC Power Extension Cable - C13 Left Angle to C14 - 2'	1
P004-002-13RA	AC Power Extension Cable - C13 Right Angle to C14 - 2 ft.	1
P036-002-20LA	2-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20 Left Angle)	1
P036-002-20RA	2-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20 Right Angle)	1
P005-12N	1-ft. (12 in.) Heavy-Duty 14AWG Power Cord (IEC-320-C13 to IEC-320-C14)	1
P005-18N	1.5-ft. (18 in.) Heavy-Duty 14AWG Power Cord (IEC-320-C13 to IEC-320-C14)	1
P005-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14)	1
P004-002-5	5-Pack of 2-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13)	1
P004-004	4-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13)	1
P004-004-BL	4-ft. 18 AWG Power Cord (IEC-320-C14 to IEC-320-C13) with Blue Connectors	1
P004-004-GN	4-ft. 18 AWG Power Cord (IEC-320-C14 to IEC-320-C13) with Green Connectors	1
P004-004-RD	4-ft. 18 AWG Power Cord (IEC-320-C14 to IEC-320-C13) with Red Connectors	1
P004-004-YW	4-ft. 18 AWG Power Cord (IEC-320-C14 to IEC-320-C13) with Yellow Connectors	1
P004-006	6-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13)	1
P004-006-2C13	6-ft. AC Power Extension Splitter Cable (C14 to 2 x C13)	1
P005-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14)	1
P005-006-BL	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14) Blue Connectors	1
P005-006-GN	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14) Green Connectors	1
P005-006-RD	6-ft. Heavy-Duty 14AWG Power Cord (IEC-320-C13 to IEC-320-C14) with Red Connectors	1
P005-006-YW	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14) Yellow Connectors	1
P004-010	10-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13)	1
P005-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14)	1
P047-002	2-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
P047-004	4-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
P047-006	6-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
P047-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
P036-006	6-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20)	1
P036-006-2C19	6-ft. AC Power Splitter Cable (C20 to 2 x C19)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4807.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.