

Horn Loudspeakers



LBC 3481/12



LBC 3491/12



LBC 3492/12



LBC 3493/12



Security Systems

EN | Installation and User Instructions
LBC 3481/12, LBC 3491/12
LBC 3492/12, LBC 3493/12

BOSCH


Technical performance data acc. to IEC 268-5

Max. power
Rated power (PHC)
Sound pressure level at rated power/1 W
(at 1 kHz, 1 m)
Effective frequency range (-10 dB)
Opening angle (at 1 kHz/4 kHz, -6dB)
Rated voltage
Rated impedance
Ambient temperature range
Water- and dust protected
Safety
Connection
Dimensions
 aperture dia.
 overall length
Colour
Weight


LBC 3481/12
15 W
10 W (10 - 5 - 2.5 W)
113 dB/103 dB (SPL)

500 Hz to 7 kHz
160°/50°
100 V
1000 Ω
-25 to +55 °C
acc. to IEC 60529 IP 65
acc. to EN 60065
4-wire cable, 2 m long


156 mm (6.14 in)
184 mm (7.24 in)
Light grey (RAL 7035)
1.25 kg (2.75 lb)



Dimensions (in mm and inches)



Circuit diagram



Frequency response

Technical performance data acc. to IEC 268-5


Max. power
Rated power (PHC)
Sound pressure level at rated power/1 W
(at 1 kHz, 1 m)
Effective frequency range (-10 dB)
Opening angle (at 1 kHz/4 kHz, -6dB)
horizontal
vertical
Rated voltage
Rated impedance
Ambient temperature range
Water- and dust protected
Safety
Connection
Dimensions
aperture
overall length
Colour
Weight

LBC 3491/12
15 W
10 W (10 - 5 - 2.5 W)
118 dB/108 dB (SPL)


480 Hz to 5.5 kHz

90°/40°
130°/45°
100 V
1000 Ω
-25 to +55 °C
acc. to IEC 60529 IP 65
acc. to EN 60065
4-wire cable, 2 m long


267 x 171 mm (10.51 x 6.73 in)
276 mm (10.87 in)
Light grey (RAL 7035)
1.4 kg (3.08 lb)



Dimensions (in mm and inches)



Circuit diagram



Frequency response


Technical performance data acc. to IEC 268-5

Max. power
Rated power (PHC)
Sound pressure level at rated power/1 W
(at 1 kHz, 1 m)
Effective frequency range (-10 dB)
Opening angle (at 1 kHz/4 kHz, -6dB)
Rated voltage
Rated impedance
Ambient temperature range
Water- and dust protected
Safety
Connection
Dimensions
 aperture dia.
 overall length
Colour
Weight


LBC 3492/12
30 W
20 W (20 - 10 - 5 W)
123 dB/110 dB (SPL)

380 Hz to 5.5 kHz
80°/35°
100 V
500 Ω
-25 to +55 °C
acc. to IEC 60529 IP 65
acc. to EN 60065
4-wire cable, 2 m long


354 mm (13.94 in)
332 mm (13.07 in)
Light grey (RAL 7035)
2.65 kg (5.83 lb)



Dimensions (in mm and inches)




Circuit diagram




Frequency response

Technical performance data acc. to IEC 268-5


Max. power	LBC 3493/12 45 W
Rated power (PHC)	30 W (30 - 15 - 7.5 W)
Sound pressure level at rated power/1 W (at 1 kHz, 1 m)	126 dB/111 dB (SPL)
Effective frequency range (-10 dB)	380 Hz to 5 kHz
Opening angle (at 1 kHz/4 kHz, -6dB)	70°/40°
Rated voltage	100 V
Rated impedance	333 Ω
Ambient temperature range	-25 to +55 °C
Water- and dust protected	acc. to IEC 60529 IP 65
Safety	acc. to EN 60065
Connection	4-wire cable, 2 m long
Dimensions	
aperture dia.	400 mm (15.75 in)
overall length	353 mm (13.90 in)
Colour	Light grey (RAL 7035)
Weight	3 kg (6.6 lbs)



Dimensions (in mm and inches)




Circuit diagram




Frequency response


LBC 3481/12




Polar diagram (measured with pink noise)



LBC 3491/12




Polar diagram vertical (measured with pink noise)




Polar diagram horizontal (measured with pink noise)

LBC 3492/12



Polar diagram (measured with pink noise)

LBC 3493/12



Polar diagram (measured with pink noise)