

GigaMax® CAT 5e Flat 110-Style Patch Panels and Patch Block

APPLICATION

GigaMax CAT 5e Flat 110-Style Patch Panels and Patch Blocks are ideal for modular cross connection and available in a multitude of port densities to meet the needs of high-speed data applications. Craft-friendly 110 punchdowns on the rear of the panel make installation easy.



SPECIFICATION

The patch panel shall meet or exceed the requirements for Category 5e described in ANSI/TIA-568-C.2 as well as the Class D requirements described in ISO/IEC 11801. The panels shall feature both T568A and T568B wiring configurations, white IDC 110-punchdown modules, mounting standoffs for cable management bars and color-coded front window labeling. The panels shall have universal T568A and T568B wiring card for terminations. The panels shall be made of 16-gauge steel, and shall have a black painted finish with white silk-screening. The plastic elements shall be fire-retardant with a UL flammability rating of 94V-0. The panel shall be offered in 12-, 24-, 48-, 96-port configurations as well as 89D 12-port configuration for wall mount applications. The patch panel shall be configured with six port modules. The 110 termination on the rear of the panel shall follow normal installation color sequence (blue, orange, green, brown) from left to right.

FEATURES

- Patented Retention Force Technology protects times from damage from 4- or 6-pin plugs
- Craft-friendly installation
- Universal T568A and T568B wiring cards for 110-style IDC terminations
- Color-coded front labeling for easy port identification (ANSI/TIA-606-B compliant)
- Terminates 26-22 AWG solid conductors
- Centralized labeling (available on 48-port) promotes greater visibility of labels when patch cords are routed into horizontal cable management above and below the patch panel
- Capable of multiple reterminations

DESIGN CONSIDERATIONS

- Mounts on 19" equipment racks
- Panel offered in 12-, 24-, 48-, 96-port configurations and 12-port U89 Block for wall mount applications
- Connector modules are in groups of six
- Includes rear cable management bars
- Use star washers for grounding in rack mount installations

STANDARDS COMPLIANCE

ANSI/TIA-568-C.2
ISO/IEC 11801
ANSI/TIA-1096-A (formerly FCC Part 68)
cULus Listed

PHYSICAL SPECIFICATIONS

Dimensions: See page 2
Capacity: 12-, 24-, 48-, or 96-port
12-Port Patch Block
U89 Universal
Materials: 16-gauge steel, painted black, PCB and plastic components are rated UL 94V-0

COUNTRY OF ORIGIN

USA


WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

5G596-Uxx, 5G596-C48

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



5G596-Uxx, 5G596-C48

PART NUMBERS

Description	Part No.
GigaMax® CAT 5e Flat 110-Style Patch Panel, 12-port, 1RU	5G596-U12
GigaMax CAT 5e Flat 110-Style Patch Panel, 24-port, 1RU	5G596-U24
GigaMax CAT 5e Flat 110-Style Patch Panel, 48-port, 2RU	5G596-U48
GigaMax CAT 5e Flat 110-Style Patch Panel, 48-Port, 2RU, Centralized Labeling	5G596-C48
GigaMax CAT 5e Flat 110-Style Patch Panel, 96-port, 4RU	5G596-U96
GigaMax CAT 5e Flat 110-Style Patch Block, 12-port	5G596-U89



Leviton Network Solutions
 2222 - 222nd St. SE
 Bothell, WA 98021-4416

Asia / Pacific
 T +1.631.812.6228
 E infoasean@leviton.com

Canada
 T +1.514.954.1840
 E pcservice@leviton.com

Caribbean
 T +1.954.593.1896
 E infocaribbean@leviton.com

China
 T +852.2774.9876
 E infochina@leviton.com

Colombia
 T +57.1.743.6045
 E infocolombia@leviton.com

tel 1-800-824-3005
 tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Europe
 T +33.6.8869.1380
 E infoeurope@leviton.com

India / SAARC
 T +91.80.4322.5678
 E infoindia@leviton.com

Mexico
 T +52.55.5082.1040
 E Isamarketing@leviton.com

Middle East & Africa
 T +971.4.886.4722
 E Imeinfo@leviton.com

South Korea
 T +82.2.3273.9963
 E infokorea@leviton.com