











Mounting




Connection





Circuit diagram




Max. power (PHC)
 6 W (6 - 3 - 1.5 W)
 9 W
 Rated power level at 6 W/1 W
 (at 1 kHz, 1 m)
 Sound pressure level at 6 W/1 W
 Effective frequency range (-10 dB)
 Opening angle (at 1 kHz/4 kHz, -6 dB)
 Rated voltage
 100 V
 1667 Ω
 -15 to +50 °C (5 to 122 °F)
 acc. to EN 60065
 2-pole push connector
 210 x 88 mm (8.3 x 3.5 in)
 182 mm (7.2 in)
 White (RAL 9010)
 1.1 kg (2.4 lb)
 Dimensions (dia. x max. depth)
 Mounting cut-out dia.
 Colour
 Weight



Max. power (PHC)
 6 W (6 - 3 - 1.5 W)
 9 W
 Rated power level at 6 W/1 W
 (at 1 kHz, 1 m)
 Sound pressure level at 6 W/1 W
 Effective frequency range (-10 dB)
 Opening angle (at 1 kHz/4 kHz, -6 dB)
 Rated voltage
 100 V
 1667 Ω
 -15 to +50 °C (5 to 122 °F)
 acc. to EN 60065
 2-pole push connector
 210 x 88 mm (8.3 x 3.5 in)
 182 mm (7.2 in)
 White (RAL 9010)
 1.1 kg (2.4 lb)
 Dimensions (dia. x max. depth)
 Mounting cut-out dia.
 Colour
 Weight

TECHNICAL PERFORMANCE DATA ACC. TO IEC 268-5

LBC 3090/01



Polar diagram



Loudspeakers



Security Systems

Instructions for use
 LBC 3090/01
 LBC 3091/01
 EN