

Enhanced Multimedia Outlet System (MOS) RCA Component Video Modules

APPLICATION

Leviton's Enhanced MOS RCA Modules provide a point-to-point connection for component video signals over twisted-pair cabling. Connect DVD players, Blu-Ray™ players, and other media sources to televisions and other displays using industry standard RCA connectors. The IDC termination allows for quick termination and customization of cable lengths in the field.

The RCA modules require a Leviton MOS wallplate. The modules are manufactured from durable ABS plastic and are available in white, ivory, or light almond.



SPECIFICATION

AV modules shall have the ability to transmit component video signals over twisted-pair cabling in a point-to-point connection. Products shall be compatible with UTP or shielded cabling that is rated for CAT 5e or higher. Twisted-pair cabling shall be terminated to product using IDC connections. Products shall be capable of transmitting video at resolutions of 1080i for distances up to 100 feet. RCA connections shall have barrel colors of red, blue, and green. Products shall be available in white, ivory, and light almond colors, and shall be compatible with Leviton Multimedia Outlet System wallplates.

FEATURES

- Provides a point-to-point RCA connection for component video signals over twisted-pair cabling (UTP or shielded)
- Twisted-pair cabling can be cut to length in field
- Twisted-pair cabling provides a migration path for future digital signals
- Fast and easy cable termination using color-coded 110-style IDC connectors

DESIGN CONSIDERATIONS

- Modules must be installed in a Leviton MOS wallplates
- RCA Component modules can be mixed with other MOS modules in the same wallplate
- One twisted-pair cable required (CAT 5e or higher, UTP or shielded)
- Component RCA modules designed to support video resolutions of 1080i for distances up to 100 feet
- RCA connectors have a 13mm (center-to-center) spacing to accommodate cords with larger plugs

MECHANICAL SPECIFICATIONS

Dimensions: 0.96" H x 1.85"W x 1.65" D

Housing Material: ABS plastic

ELECTRICAL SPECIFICATIONS

Cable Type: UTP and shielded twisted-pair (CAT 5e or higher)

Cable length: Up to 100 feet (1080i)

Impedance: RCA – 75 Ω unbalanced
IDC – 100 Ω balanced

ELECTRICAL SPECIFICATIONS

Operating Temperature: 0° C to 50° C (32° F to 122° F)

Storage Temperature: -10° C to 70° C (14° F to 158° F)

Relative Humidity: 0% to 90%, non-condensing

REGULATORY

UL 1863 UL 94V-0

COUNTRY OF ORIGIN

Taiwan


WARRANTY INFORMATION

One-year limited warranty.

For a copy of Leviton product warranties, visit www.leviton.com.


ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.




CONNECTOR PIN-OUT

Signal	IDC/Wire
n/a	brown
n/a	w/brown
Red RCA center	green
Red RCA ground	w/green
Blue RCA center	orange
Blue RCA ground	w/orange
Green RCA center	blue
Green RCA ground	w/blue



WIRING DIAGRAM



PART NUMBERS	
Description	Part No.
RCA Component Video MOS Module, 110-style termination, white	41292-DEW
RCA Component Video MOS Module, 110-style termination, ivory	41292-DEI
RCA Component Video MOS Module, 110-style termination, light almond	41292-DET

Leviton Network Solutions 2222 - 222nd St. SE Bothell, WA 98021-4416 tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	Asia / Pacific T +1.631.812.6228 E infoasean@leviton.com	Canada T +1.514.954.1840 E pcservice@leviton.com	Caribbean T +1.954.593.1896 E infocaribbean@leviton.com	China T +852.2774.9876 E infochina@leviton.com	Colombia T +57.1.743.6045 E infocolombia@leviton.com
	Europe T +33.6.8869.1380 E infoeurope@leviton.com	India / SAARC T +91.80.4322.5678 E infoindia@leviton.com	Mexico T +52.55.5082.1040 E lsamarketing@leviton.com	Middle East & Africa T +971.4.886.4722 E lmeinfo@leviton.com	South Korea T +82.2.3273.9963 E infokorea@leviton.com