

QuickPort® Modular Furniture Faceplates with ID Windows

APPLICATION

Leviton's QuickPort® Modular Furniture Faceplates with ID windows offer field-configurable flexibility, and feature a designation window for simpler, more organized workstation identification. The faceplates accept QuickPort snap-in connectors and adapters to support a variety of voice/data applications in open office environments.

FEATURES

- Installation and changes can be made without removing the modular furniture channel cover.
- Plate can be installed and removed from kickplate without tools (see detailed installation instructions included with product).
- ID designation window for each faceplate.
- Labeling kit included (contains two, white labels).

STANDARDS COMPLIANCE

Meets or exceeds all applicable standards: cULus Listed; complies with NEC® Article 800 and TIA/EIA-568-B.

PHYSICAL SPECIFICATIONS

Dimensions: Standard: 1.70"H x 3.15"W x 1.18"D*
Herman Miller: 2.18"H x 3.65"W x 1.18"D*
Extended-Depth: 1.80"H x 3.25"W x 1.18"D*
**when loaded with a Category 5 connector*
Designation Label: 1.83"H x .45"W x .93"D

Capacity: Four-port versions accept any combination of 1 to 4 QuickPort connectors and adapters. Two-port versions accept 1 or 2 connectors and adapters in any combination

Materials: High-impact, fire-retardant plastic rated UL 94V-0

DESIGN CONSIDERATIONS

- Specify 49910-SXX (standard) or 49910-HXX (Herman Miller) versions (dependent on furniture type).*
- Specify 49910-EXX (same opening size as 49910-SXX) for installation into shallow raceway channels (plate has 0.5" added depth).
- Specify port identification method (colored connectors, adapters, and designation labels available).
- Configure 1, 2, 3 or 4 active ports; spare ports can be filled with blanks for later use (one blank QuickPort insert is included with 4-port plate).

*XX=various configurations and colors, see second page.

See ELECTRONIC FILES for CAD files (.DXF, .DWG, MS-DOS.EPS) on disk



WARRANTY INFORMATION

For a copy of Leviton product warranties, log on to www.levitonvoicedata.com/warranty.

For ELECTRONIC Typical Specs see (.TXT) file on disk.

TYPICAL SPECIFICATION

QuickPort Modular Furniture Faceplate—Standard

The modular furniture connector housing must be a field-configurable faceplate providing from 1 to 4 flush-mount ports for a variety of snap-in connectors and adapters.

QuickPort Modular Furniture Faceplate—Herman Miller

The modular furniture connector housing must be a field-configurable flush-mount faceplate compatible with Herman Miller voice/data openings, and providing from 1 to 4 flush-mount ports for a variety of snap-in connectors and adapters.

QuickPort Modular Furniture Faceplate—Extended-Depth

The modular furniture connector housing must be a field-configurable faceplate extending 0.75" from the furniture raceway to facilitate fiber or copper cable bend-radius compliance, or to compensate for shallow/crowded/powered raceway channels, and providing from 1 to 4 flush-mount ports for a variety of snap-in connectors and adapters.

Faceplate must have a rattle-free fit and a single tool-less release latch; be constructed of high-impact self-extinguishing plastic rated UL 94V-0; and be cULus Listed, and compliant with FCC Part 68, NEC Article 800 and TIA/EIA-568-B specifications.



For Technical Support Call 1-425-485-4288; in USA call 1-800-824-3005.
Spec sheets and updates are also available at www.levitonvoicedata.com.

2222 - 222nd St. SE • Bothell, WA 98021 USA
Tel: 1-800-722-2082 / 1-425-485-4288 • Fax: 1-425-483-5270 • Int'l Fax: 1-425-485-9170 • GSA Schedule Available.




QuickPort® Modular Furniture Faceplates

Part Number
49910-xxx

DIMENSIONAL LINE ART


See ELECTRONIC FILES for CAD images
(.DXF, .DWG, MS-DOS.EPS)

Standard Faceplate
(-S*2, -S*4 versions)




Front View

Herman Miller Faceplate
(-H*2, -H*4 versions)




Front View

Extended-Depth Faceplate
(-E*4 versions)




Front View




STANDARD FACEPLATE
2- or 4-Port
(fits openings
of approximately
1.38" x 2.70")

Side View



**HERMAN MILLER
FACEPLATE**
2- or 4-port
(fits openings of
approximately
1.88" x 2.98")

Side View



**EXTENDED-DEPTH
FACEPLATE**
4-port only for shallow
or powered channels
(fits openings of
approximately
1.38" x 2.70")

Side View

PART NUMBERS

Description	Part No.	Herman Miller	Steelcase	Haworth	HON	Others
2-Port Faceplate w/ ID Window	49910-S*2	✓	✓	✓	✓	✓
4-Port Faceplate w/ ID Window (includes one blank)	49910-S*4	✓	✓	✓	✓	✓
4-Port Extended Faceplate w/ID Window (includes one blank)	49910-E*4	✓	✓	✓	✓	✓

(Above part numbers fit openings of approx. 1.38" x 2.70")
*Colors Choices = (I) Ivory, (W) White, (G) Grey and (E) Black

Description	Part No.	Herman Miller	Steelcase	Haworth	HON	Others
2-Port HM Faceplate w/ ID Window	49910-H*2	✓	-	-	-	✓
4-Port HM Faceplate w/ ID Window (includes one blank)	49910-H*4	✓	-	-	-	✓

(Above part numbers fit openings of approx. 1.88" x 2.98")
*Colors Choices = (I) Ivory, (W) White, (G) Grey and (E) Black



For Technical Support Call 1-425-485-4288; in USA call 1-800-824-3005.
Spec sheets and updates are also available at www.levitonvoicedata.com.



2222 - 222nd St. SE • Bothell, WA 98021 USA • Tel: 1-800-722-2082 / 1-425-485-4288 • Fax: 1-425-483-5270 • Int'l Fax: 1-425-485-9170 • GSA Schedule Available.