

## Rapid Transit



### Product Description

Thermoset polyolefin insulation  
Single stranded conductor  
UL VW-1, IEEE 383

### Applications

Internal wiring for rapid transit cars and heavy and light rail cars. Also used in diesel electric locomotives, wayside equipment and offroad vehicles.

### Specifications

- CONDUCTOR: Tinned, stranded copper
- INSULATION: Polyolefin (radiation Cross-Linked)
- STANDARDS: Passes VW-1 vertical flame test UL Standard 44, ICEA S-95-658 (NEMA WC70)
- TEMPERATURE: 110°C for car wiring, 125°C for locomotive cable
- VOLTAGE: 2,000 V

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

Part No.	Conductor Size AWG	No. of Strands	Insulation Thickness (in.)	Overall Jacket Thickness (in.)	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.	Amps per Conductor 110°C	Amps per Conductor 125°C
2XT-1801	18	19	0.045	0.052	0.150	17	30	32
2XT-1601	16	19	0.045	0.060	0.160	19	35	38
2XT-1401	14	19	0.045	0.070	0.175	25	41	44
2XT-1201	12	19	0.045	0.090	0.195	34	52	56
2XT-1001	10	27	0.045	0.123	0.230	52	73	79
2XT-0601	6	61	0.055	0.180	0.330	113	120	130
2XT-0501	5	91	0.055	0.220	0.365	153	160	173
2XT-0401	4	105	0.055	0.240	0.345	174	168	181
2XT-0301	3	125	0.055	0.260	0.410	204	199	215
2XT-0201	2	150	0.055	0.325	0.450	235	214	231
2XT-0101	1	225	0.065	0.390	0.535	363	268	289
2XT-1011	1/0	275	0.065	0.420	0.585	435	304	328
2XT-2021	2/0	325	0.065	0.460	0.630	489	338	364
2XT-3031	3/0	450	0.065	0.565	0.715	673	414	446
2XT-4041	4/0	550	0.065	0.590	0.770	815	472	509
2XT-2621	262	650	0.075	0.660	0.835	975	524	565
2XT-3131	313	775	0.075	0.740	0.900	1,164	590	636
2XT-3731	373	925	0.075	0.790	0.980	1,349	657	708
2XT-4441	444	1,100	0.075	0.870	1.045	1,630	734	791
2XT-5351	535	1,325	0.090	0.970	1.175	2,018	828	893
2XT-6461	646	1,600	0.090	1.060	1.265	2,311	931	1,004
2XT-7771	777	1,925	0.090	1.120	1.345	2,777	1,047	1,129
2XT-9291	929	2,300	0.090	1.230	1.455	3,443	1,168	1,259
2XT-11111	111	2,750	0.110	1.370	1.625	3,980	1,254	1,352

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.