

XLP/PVC Wire Shield



Product Description

XLP insulation

PVC jacket

Shielded

100% insulation level

Applications

For use in power circuits up to 5 kV when installed in open air, conduit, duct, or buried direct in earth, for wet and dry locations.

Used for power applications in chemical plants, refineries, steel mills, industrial plants, utility substations, and generating stations.

Specifications

- CONDUCTOR: Class B stranded, annealed, bare copper per ASTM B-3 and B-8, strand shield is an extruded semiconducting compound
- INSULATION: Cross-Linked Polyethylene (XLP) per ICEA S-93-639 (NEMA WC74)
- INSULATION SHIELD: Semiconducting layer with copper shielding wires meeting the requirements of ICEA S-93-639
- OVERALL JACKET: Sunlight-resistant, black Polyvinyl Chloride (PVC) in accordance with ICEA S-93-639
- STANDARDS: Listed by UL as Type MV-90 cable per Standard 1072, meets requirements of ICEA S-93-639
- AMPACITY: Based on three single conductor cables in isolated conduit in air per NEC Table 310.73 with a conductor temperature of 90°C and an ambient temperature of 40°C
- TEMPERATURE: 90°C
- VOLTAGE: 5 kV

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

Diameters and weights may vary among manufacturers.

Part No.	Conductor Size AWG/kcmil	No. of Strands	Insulation Thickness (in.)	Nom. Insulation O.D. (in.)	Overall Jacket Thickness (in.)	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.	Amps per Conductor
3D-0601	6	7	0.090	0.38	0.060	0.600	195	75
3D-0401	4	7	0.090	0.42	0.060	0.650	255	97
3D-0201	2	7	0.090	0.48	0.060	0.700	345	130
3D-1011	1/0	19	0.090	0.56	0.060	0.780	485	180
3D-2021	2/0	19	0.090	0.60	0.080	0.870	620	205
3D-4041	4/0	19	0.090	0.71	0.080	0.980	890	280
3D-2501	250	37	0.090	0.76	0.080	1.020	1,025	315
3D-3501	350	37	0.090	0.86	0.080	1.130	1,360	385
3D-5001	500	37	0.090	0.99	0.080	1.250	1,860	475
3D-7501	750	61	0.090	1.17	0.080	1.440	2,790	600
3D-10001	1000	61	0.090	1.32	0.080	1.580	3,550	690

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.