

Outside Plant Aerial Cable



Product Description

For use in exchange and campus areas, supported by a pre-installed messenger. Suitable for voice frequency, both analog and digital, on a selected pair assignment basis.

Specifications

- Solid, annealed, bare copper conductors
- Solid polyolefin conductor insulation color-coded to telephone industry standards
- Insulated conductors are twisted into pairs of varying lengths of lay to minimize crosstalk
- Pairs are stranded into units (and super units if required by pair count) and the resultant cable core is covered with a non-hygroscopic tape. In cable sizes of 1,200 pair and greater, a mirror-image super unit-color-code system is adopted
- The ALPETH cable sheath consists of 0.008 in., corrugated, aluminum shield and a black polyethylene jacket. The jacket is sequentially printed with a footage marker at regular intervals

Tech. Info & Standards

Cable conforms to Bellcore specifications.

Part No.	Bell Code	No. of Pairs	AWG	Standard Length (ft.)	Nom. O.D. (in.)	Approx. Wt. lb./ft.
E-002524AAA	BKMA	25	24	8,000	0.520	0.13
E-005024AAA	BKMA	50	24	8,000	0.660	0.22
E-010024AAA	BKMA	100	24	8,000	0.880	0.39
E-020024AAA	BKMA	200	24	5,700	1.130	0.72
E-030024AAA	BKMA	300	24	5,000	1.380	1.02
E-040024AAA	BKMA	400	24	4,000	1.540	1.41
E-060024AAA	BKMA	600	24	3,100	1.830	2.05
E-090024AAA	BKMA	900	24	1,680	2.210	3.01

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.