















CHATSWORTH PRODUCTS, INC.

Optimize.
Store.
Secure.



Cable Pathway Products

					
Universal Cable Runway	UL Classified Cable Runway	Runway Splices, Turns & Supports	OnTrac® Shaped Wire Cable Tray	OnTrac® Standard Wire Cable Tray	OnTrac® Splices, Turns & Supports
<p>Application: Use in telecommunication rooms, equipment rooms, and data centers</p>	<p>Application: Simplifies the cable runway grounding and bonding process</p>	<p>Application: Connect and support Cable Runway to form a continuous pathway for cables</p>	<p>Application: Use for high density cable distribution in data centers and computer rooms</p>	<p>Application: Use for premise cable distribution and in network equipment rooms and data centers</p>	<p>Application: Connect and support OnTrac Cable Tray to form a continuous pathway for cables</p>
<p>Key Features:</p> <ul style="list-style-type: none"> • UL Classified for suitability as an equipment grounding conductor only • Remove paint to bond cable runway sections with splices or ground straps • 9 sizes • No side walls, 1-1/2" (38 mm) high stringers • 12" (300 mm) rung spacing 	<p>Key Features:</p> <ul style="list-style-type: none"> • UL Classified for suitability as an equipment grounding conductor only • Splices bond cable runway sections - a separate bonding step is not required • 7 sizes • No side walls, 1-1/2" (38 mm) high stringers • 9" (230 mm) rung spacing 	<p>Key Features:</p> <ul style="list-style-type: none"> • Support cable runway from the ceiling, wall, floor or tops of racks and cabinets • Connect Cable Runway end-to-end with Butt Splice Kits • Create 90° L- or T-shaped intersections with Junction Splice Kits • Use E-Bends and Corner Brackets to make smooth turns • Change elevations with Radius Bends • Add Cable Retaining Posts when cables are stacked over 2" (50 mm) high • Use Radius Drop wherever cables exit the pathway 	<p>Key Features:</p> <ul style="list-style-type: none"> • Unique flattened cross supports provide a larger contact surface for cables and reduce cable strain where cables cross tray wires • UL Classified for suitability as an equipment grounding conductor only • 22 sizes • Side Walls: 2" (50 mm), 4" (100 mm) or 6" (150 mm) high • 2" x 4" (50 mm x 100 mm) wire mesh 	<p>Key Features:</p> <ul style="list-style-type: none"> • Support horizontal and backbone fiber and copper cables overhead or under (raised) access floors • UL Classified for suitability as an equipment grounding conductor only • 22 sizes • Side Walls: 2" (50 mm), 4" (100 mm) or 6" (150 mm) high • 2" x 4" (50 mm x 100 mm) wire mesh 	<p>Key Features:</p> <ul style="list-style-type: none"> • Support Shaped or Standard OnTrac Wire Cable Tray from the ceiling, wall, floor or the tops of racks and cabinets • Use above drop ceilings or below raised access floors • Cut and form OnTrac Wire Mesh Cable Tray to create smooth turns and changes in elevation • Use splice kits to bolt and electrically bond sections of wire mesh tray together
<p>Widths (9):</p> <ul style="list-style-type: none"> • 4" (100 mm) • 6" (150 mm) • 9" (230 mm) • 12" (300 mm) • 15" (380 mm) • 18" (460 mm) • 24" (610 mm) • 30" (760 mm) • 36" (910 mm) 	<p>Widths (7):</p> <ul style="list-style-type: none"> • 6" (150 mm) • 9" (230 mm) • 12" (300 mm) • 15" (380 mm) • 18" (460 mm) • 20" (510 mm) • 24" (610 mm) 		<p>Widths (8):</p> <ul style="list-style-type: none"> • 4" (100 mm) • 6" (150 mm) • 8" (200 mm) • 12" (300 mm) • 16" (400 mm) • 18" (450 mm) • 20" (500 mm) • 24" (600 mm) 	<p>Widths (8):</p> <ul style="list-style-type: none"> • 4" (100 mm) • 6" (150 mm) • 8" (200 mm) • 12" (300 mm) • 16" (400 mm) • 18" (450 mm) • 20" (500 mm) • 24" (600 mm) 	
<p>Length:</p> <ul style="list-style-type: none"> • 119.5" (3035 mm) 9' - 11.5" (3 m) 	<p>Length:</p> <ul style="list-style-type: none"> • 116.5" (2959 mm) 9' - 8.5" (2.9 m) 		<p>Length:</p> <ul style="list-style-type: none"> • 118" (2997 mm) 10'L (3 m) 	<p>Length:</p> <ul style="list-style-type: none"> • 118" (2997 mm) 10'L (3 m) 	
<p>Support Spacing:</p> <ul style="list-style-type: none"> • Every 5' (1.5 m) of span and within 2' (0.6 m) of any intersection 	<p>Support Spacing:</p> <ul style="list-style-type: none"> • Every 5' (1.5 m) of span and within 2' (0.6 m) of any intersection 		<p>Support Spacing:</p> <ul style="list-style-type: none"> • Every 6' (1.8 m) of span and within 2' (0.6 m) of any intersection 	<p>Support Spacing:</p> <ul style="list-style-type: none"> • Every 6' (1.8 m) of span and within 2' (0.6 m) of any intersection 	
<p>Construction:</p> <ul style="list-style-type: none"> • Welded steel, painted finish 	<p>Construction:</p> <ul style="list-style-type: none"> • Welded steel, zinc-plated finish 	<p>Construction:</p> <ul style="list-style-type: none"> • Welded or formed steel, zinc-plated or painted finish 	<p>Construction:</p> <ul style="list-style-type: none"> • Welded steel, pre-galvanized or black painted finish 	<p>Construction:</p> <ul style="list-style-type: none"> • Welded steel, pre-galvanized, black painted or zinc plated finish 	<p>Construction:</p> <ul style="list-style-type: none"> • Welded or formed steel, pre-galvanized, black painted or zinc plated finish



Universal Cable Runway

UL Classified Cable Runway

Runway Splices, Turns & Supports

OnTrac® Shaped Wire Cable Tray

OnTrac® Standard Wire Cable Tray

OnTrac® Splices, & Supports

Part No.	Description	Wt.
10250-X04	1.5"H x 4"W x 9'-11.5"L 38 mm x 100 mm x 3 m	18 lb 8.2 kg
10250-X06	1.5"H x 6"W x 9'-11.5"L 38 mm x 150 mm x 3 m	19 lb 8.6 kg
10250-X09	1.5"H x 9"W x 9'-11.5"L 38 mm x 230 mm x 3 m	20 lb 9.1 kg
10250-X12	1.5"H x 12"W x 9'-11.5"L 38 mm x 300 mm x 3 m	25 lb 11.3 kg
10250-X15	1.5"H x 15"W x 9'-11.5"L 38 mm x 380 mm x 3 m	27 lb 12.2 kg
10250-X18	1.5"H x 18"W x 9'-11.5"L 38 mm x 460 mm x 3 m	29 lb 13.2 kg
10250-X24	1.5"H x 24"W x 9'-11.5"L 38 mm x 610 mm x 3 m	32 lb 14.5 kg
10250-X31	1.5"H x 30"W x 9'-11.5"L 38 mm x 760 mm x 3 m	35 lb 15.7 kg
10250-X37	1.5"H x 36"W x 9'-11.5"L 38 mm x 910 mm x 3 m	38 lb 17.2 kg

Note: X=Color: (-1XX)=Gray, (-2XX)=White, (-7XX)=Black.

Key Accessories

Part No.	Description	Wt.
16301-001	Butt-Splice Kit	1 lb 0.5 kg
16302-001	Junction-Splice Kit	1 lb 0.5 kg
40164-025	Ground Strap Kit Pack of 25	12 lb 5.0 kg
11959-X15	Corner Bracket, 15"W (380 mm)	4 lb 1.8 kg
10822-X12	E-Bend, 12"W (300 mm)	12 lb 5.4 kg
10723-X12	Outside Radius Bend, 12"W (300 mm)	4 lb 1.8 kg
10724-X12	Inside Radius Bend, 12"W (300 mm)	4 lb 1.8 kg
10596-X58	Cable Retaining Post, 8"H (200 mm), Pack of 50	33 lb 15.0 kg
12100-X06	Radius Drop, 6"W (150 mm)	2 lb 0.9 kg
13392-712	Cable Runway Dividers Pack of 25	3 lb 1.4 kg
13395-X04	Patch Rack, 4U x 19"W w/Side Stringer Brackets	5 lb 2.3 kg

Part No.	Description	Wt.
11275-006	1.5"H x 6"W x 9'-8.5"L 38 mm x 150 mm x 2.9 m	19 lb 8.6 kg
11275-009	1.5"H x 9"W x 9'-8.5"L 38 mm x 230 mm x 2.9 m	20 lb 9.1 kg
11275-012	1.5"H x 12"W x 9'-8.5"L 38 mm x 300 mm x 2.9 m	22 lb 10.0 kg
11275-015	1.5"H x 15"W x 9'-8.5"L 38 mm x 380 mm x 2.9 m	26 lb 11.8 kg
11275-018	1.5"H x 18"W x 9'-8.5"L 38 mm x 460 mm x 2.9 m	28 lb 12.7 kg
11275-020	1.5"H x 20"W x 9'-8.5"L 38 mm x 510 mm x 2.9 m	29 lb 13.2 kg
11275-024	1.5"H x 24"W x 9'-8.5"L 38 mm x 610 mm x 2.9 m	31 lb 14.1 kg

Note: Color is Gold chem film over zinc plating.

Key Accessories

Part No.	Description	Wt.
16301-001	Butt-Splice Kit	1 lb 0.5 kg
16302-001	Junction-Splice Kit	1 lb 0.5 kg
11959-015	Corner Bracket, 15"W (380 mm)	4 lb 1.8 kg
10822-012	E-Bend, 12"W (300 mm)	12 lb 5.4 kg
10723-012	Outside Radius Bend, 12"W (300 mm)	4 lb 1.8 kg
10724-012	Inside Radius Bend, 12"W (300 mm)	4 lb 1.8 kg
10596-058	Cable Retaining Post, 8"H (200 mm), Pack of 50	33 lb 15.0 kg
13392-712	Cable Runway Dividers Pack of 25, Black	3 lb 1.4 kg
13395-704	Patch Rack, 4U x 19"W w/Side Stringer Brackets	5 lb 2.3 kg

Part No.	Description	Wt.
Triangle Support Bracket		
11746-X12	Wall Support, Side, for 12"W (300 mm) Runway	5 lb 2.3 kg
11746-X18	Wall Support, Side, for 18"W (460 mm) Runway	8 lb 3.6 kg
11746-X24	Wall Support, Side, for 24"W (610 mm) Runway	9 lb 4.1 kg
Wall Angle Support Kit		
11421-X12	Wall Support, End, for 12"W (300 mm) Runway	3 lb 1.4 kg
11421-X18	Wall Support, End, for 18"W (460 mm) Runway	5 lb 2.3 kg
11421-X24	Wall Support, End, for 24"W (610 mm) Runway	6 lb 2.7 kg
Center Support Kit		
12362-X12	Ceiling Support, for 12"W (300 mm) Runway	2 lb 0.9 kg
12362-X18	Ceiling Support, for 18"W (460 mm) Runway	4 lb 1.8 kg
12362-X24	Ceiling Support, for 24"W (610 mm) Runway	5 lb 2.3 kg

3" Channel Rack-To-Runway Mounting Plate		
10595-X12	Rack-Top Support, for 12"W (300 mm) Runway	5 lb 2.3 kg
10595-X18	Rack-Top Support, for 18"W (460 mm) Runway	7 lb 3.2 kg
12408-X24	Rack-Top Support, for 24"W (610 mm) Runway	4 lb 1.8 kg

(-024) not available. Use with CPI Standard and Universal Racks.

Elevation Kit for 2-Post Racks		
10506-X02	Elevates Runway, 2"H (50 mm), 2.5"H (64 mm) or 3"H (80 mm)	2 lb 0.9 kg
10506-X06	Elevates Runway, 4"H (100 mm), 5"H (130 mm) or 6"H (150 mm)	5 lb 2.3 kg

Use with Rack-To-Runway Mounting Plate.

Note: X=Color: (-0XX)=Gold, (-1XX)=Gray, (-2XX)=White and (-7XX)=Black.

Contact Tech Support at 800-834-4969 for assistance specifying splices and supports.

Part No.	Description	Wt.
36811-604	2"H x 4"W x 10'L 50 mm x 100 mm x 3 m	11 lb 5.0 kg
36811-606	2"H x 6"W x 10'L 50 mm x 150 mm x 3 m	12 lb 5.4 kg
36811-608	2"H x 8"W x 10'L 50 mm x 200 mm x 3 m	14 lb 6.4 kg
36811-612	2"H x 12"W x 10'L 50 mm x 300 mm x 3 m	17 lb 7.7 kg
36811-616	2"H x 16"W x 10'L 50 mm x 400 mm x 3 m	20 lb 9.1 kg
36811-618	2"H x 18"W x 10'L 50 mm x 450 mm x 3 m	21 lb 9.5 kg
36811-620	2"H x 20"W x 10'L 50 mm x 500 mm x 3 m	23 lb 10.6 kg
36811-624	2"H x 24"W x 10'L 50 mm x 600 mm x 3 m	26 lb 11.8 kg
36821-604	4"H x 4"W x 10'L 100 mm x 100 mm x 3 m	14 lb 6.4 kg
36821-606	4"H x 6"W x 10'L 100 mm x 150 mm x 3 m	16 lb 7.3 kg
36821-608	4"H x 8"W x 10'L 100 mm x 200 mm x 3 m	18 lb 8.7 kg
36821-612	4"H x 12"W x 10'L 100 mm x 300 mm x 3 m	21 lb 9.5 kg
36821-616	4"H x 16"W x 10'L 100 mm x 400 mm x 3 m	24 lb 10.9 kg
36821-618	4"H x 18"W x 10'L 100 mm x 450 mm x 3 m	25 lb 11.3 kg
36821-620	4"H x 20"W x 10'L 100 mm x 500 mm x 3 m	27 lb 12.2 kg
36821-624	4"H x 24"W x 10'L 100 mm x 600 mm x 3 m	30 lb 13.6 kg
36831-608	6"H x 8"W x 10'L 150 mm x 200 mm x 3 m	22 lb 10.0 kg
36831-612	6"H x 12"W x 10'L 150 mm x 300 mm x 3 m	25 lb 11.3 kg
36831-616	6"H x 16"W x 10'L 150 mm x 400 mm x 3 m	28 lb 12.7 kg
36831-618	6"H x 18"W x 10'L 150 mm x 450 mm x 3 m	29 lb 13.2 kg
36831-620	6"H x 20"W x 10'L 150 mm x 500 mm x 3 m	31 lb 14.1 kg
36831-624	6"H x 24"W x 10'L 150 mm x 600 mm x 3 m	34 lb 15.4 kg

Note: The above part numbers have a pre-galvanized finish (-6XX). Black painted finish (-7XX) is also available. 4"W (100 mm) not UL Classified.

Part No.	Description	Wt.
34811-604	2"H x 4"W x 10'L 50 mm x 100 mm x 3 m	11 lb 5.0 kg
34811-606	2"H x 6"W x 10'L 50 mm x 150 mm x 3 m	12 lb 5.4 kg
34811-608	2"H x 8"W x 10'L 50 mm x 200 mm x 3 m	14 lb 6.4 kg
34811-612	2"H x 12"W x 10'L 50 mm x 300 mm x 3 m	17 lb 7.7 kg
34811-616	2"H x 16"W x 10'L 50 mm x 400 mm x 3 m	20 lb 9.1 kg
34811-618	2"H x 18"W x 10'L 50 mm x 450 mm x 3 m	21 lb 9.5 kg
34811-620	2"H x 20"W x 10'L 50 mm x 500 mm x 3 m	23 lb 10.6 kg
34811-624	2"H x 24"W x 10'L 50 mm x 600 mm x 3 m	26 lb 11.8 kg
34821-604	4"H x 4"W x 10'L 100 mm x 100 mm x 3 m	14 lb 6.4 kg
34821-606	4"H x 6"W x 10'L 100 mm x 150 mm x 3 m	16 lb 7.3 kg
34821-608	4"H x 8"W x 10'L 100 mm x 200 mm x 3 m	18 lb 8.7 kg
34821-612	4"H x 12"W x 10'L 100 mm x 300 mm x 3 m	21 lb 9.5 kg
34821-616	4"H x 16"W x 10'L 100 mm x 400 mm x 3 m	24 lb 10.9 kg
34821-618	4"H x 18"W x 10'L 100 mm x 450 mm x 3 m	25 lb 11.3 kg
34821-620	4"H x 20"W x 10'L 100 mm x 500 mm x 3 m	27 lb 12.2 kg
34821-624	4"H x 24"W x 10'L 100 mm x 600 mm x 3 m	30 lb 13.6 kg
34831-608	6"H x 8"W x 10'L 150 mm x 200 mm x 3 m	22 lb 10.0 kg
34831-612	6"H x 12"W x 10'L 150 mm x 300 mm x 3 m	25 lb 11.3 kg
34831-616	6"H x 16"W x 10'L 150 mm x 400 mm x 3 m	28 lb 12.7 kg
34831-618	6"H x 18"W x 10'L 150 mm x 450 mm x 3 m	29 lb 13.2 kg
34831-620	6"H x 20"W x 10'L 150 mm x 500 mm x 3 m	31 lb 14.1 kg
34831-624	6"H x 24"W x 10'L 150 mm x 600 mm x 3 m	34 lb 15.4 kg

Note: The above part numbers have a pre-galvanized finish (-6XX). Black painted finish (-7XX) and zinc electroplate (-5XX) finish are also available. 4"W (100 mm) not UL Classified.

Part No.	Description	Wt.
34738-501	Standard Splice Kit, 50 Pk	11 lb 5.0 kg
34740-501	90° Splice Bar Kit	2 lb 0.9 kg

Note: Use Standard Splice Kit to make turns and end-to-end connections. Use 90° Splice Bar Kit to make (1) T-splice or (2) L-splices.

34730-612	Trapeze Support Brkt, 12"W (300 mm)	2 lb 0.9 kg
34730-624	Trapeze Support Brkt, 24"W (600 mm)	3 lb 1.4 kg
34735-612	Wall-Mount Angle, 12"W (300 mm)	1 lb 0.5 kg
34735-624	Wall-Mount Angle, 24"W (600 mm)	2 lb 0.9 kg
34733-612	Triangle Support Brkt, 12"W (300 mm)	2 lb 0.9 kg
34733-624	Triangle Support Brkt, 24"W (600 mm)	4 lb 1.8 kg
34737-502	Pedestal Clamp Brkt Kit, 2' (0.6 m) Floor	4 lb 1.8 kg

Note: Support Trapeze Support Bracket with 3/8" (M10) threaded rod and hardware. Attach Wall-Mount Angle with 1/4" (M6) hardware. Attach Triangle Support Bracket with 3/8" (M10) hardware. Pedestal Clamp Support Kit attaches to 1" to 2" round pedestals.

Key Accessories

Part No.	Description	Wt.
34741-501	Toolless Radius Drop, 7.75"W (197 mm)	1 lb 0.5 kg
34838-001	Split Bolt Grounding Clamp, 10 Pack	1 lb 0.5 kg
34749-001	Label Holder, 10 Pack	1 lb 0.5 kg
34839-001	Cable Tray Cutting Tool	6 lb 2.7 kg

Note: Other supports are available.

Contact Tech Support at 800-834-4969 for assistance specifying splices and supports.



www.chatsworth.com • techsupport@chatsworth.com • +1-800-834-4969

©2012 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, GlobalFrame, Cube-IT Plus, Evolution, OnTrac, QuadraRack and Velocity are federally registered trademarks of Chatsworth Products, Inc. eConnect and Simply Efficient are trademarks of Chatsworth Products, Inc. All other trademarks belong to their respective companies. Rev.10 06/12 MKT-60020-292