


Fire Alarm Nonshielded Plenum



Product Description

Power limited fire alarm and communications cable for riser or nonriser applications. Fire alarm, smoke detectors, signaling and fire-protective circuits. XX in part number denotes color; call your local sales representative for specific requirements.

Specifications

- CONDUCTOR: Solid or stranded bare copper
- INSULATION: FRPVC
- JACKET: FRPVC with rip cord
- STANDARDS: NEC FPLP, UL Listed
- TEMPERATURE: 75°C

Tech. Info & Standards

PVC
Solid conductor
FPLP, UL Listed

Part No.	Conductor Size AWG	No. of Conductors	Insulation Thickness (in.)	Jacket Thickness (in.)	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.
FA-1202C-1-2N-XX	12	2	0.011	0.015	0.238	58
FA-1202C-2-2N-XX	12	2 Stranded	0.011	0.015	0.239	58
FA-1402C-1-2N-XX	14	2	0.011	0.015	0.202	38
FA-1402C-2-2N-XX	14	2 Stranded	0.011	0.015	0.203	38
FA-1404C-1-2N-XX	14	4	0.011	0.015	0.236	71
FA-1602C-1-2N-XX	16	2	0.010	0.015	0.173	26
FA-1604C-1-2N-XX	16	4	0.010	0.015	0.204	48
FA-1802C-1-2N-XX	18	2	0.010	0.015	0.152	18
FA-1802C-2-2N-XX	18	2 Stranded	0.010	0.015	0.154	20
FA-1804C-1-2N-XX	18	4	0.010	0.015	0.177	34
FA-1806C-1-2N-XX	18	6	0.010	0.015	0.240	49
FA-2204C-1-2N-XX	22	4	0.009	0.015	0.122	16

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.