


1422/1423 (0.005-0.004 in. Wall, Voltage - Not Specified)

**Product Description**

Kynar
Solid conductor

Applications

Insulated solid conductor copper wire for "back panel" wiring of computers and other electronic applications where solderless wraps are used.

Specifications

- CONDUCTOR: Silver-coated, solid conductor copper
- INSULATION: Kynar, 0.005 in. wall (UL 1422) or 0.004 in. wall (UL 1423)
- STANDARDS: UL recognized AWM Style 1422/1423 per UL 758 requirements
- TEMPERATURE: 105°C
- VOLTAGE: Not rated

All part numbers require color code designation. Diameters and weights may vary among manufacturers.

Part No.	Conductor AWG	Stranding No. x AWG	Conductor Nom. Dia.	Wire O.D.	Approx. Wt. lb./1,000 ft.
1422-30/1-XX	30	Solid	0.010	0.020	0.5
1422-28/1-XX	28	Solid	0.013	0.023	0.8
1422-26/1-XX	26	Solid	0.016	0.027	1.0
1422-22/1-XX	22	Solid	0.020	0.031	1.6

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

Insulation Color Code Chart

0.....black
1.....brown
2.....red
3.....orange
4.....yellow
5.....green
6.....blue
7.....violet/purple
8.....gray
9.....white
P.....pink
T.....tan
D.....dark (i.e. D6=dark blue)
L.....light (i.e. L6=light blue)

For white with black stripe - 90

For green with yellow stripe - 54

For white with a black and red stripe - 902

For white and black twisted conductor - 9/0

For white, black and red twisted conductors - 9/0/2

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.