

MG

**Product Description**

Mica glass composite insulation

Fiberglass braid jacket

600 V

UL AWM Style 5107/5335

Applications

Wiring of very high-temperature commercial or industrial equipment. Useful for high-temperature environments where lower-rated cables will not work adequately.

Specifications

- CONDUCTOR: Nickel-plated copper per ASTM B-355, Class K stranded per ASTM B-174 or Class H stranded per ASTM B-173
- INSULATION: Mica glass composite or tape
- OVERALL JACKET: Braided-glass yarn impregnated with high-temperature finish
- STANDARDS: UL Listed for 450°C with a 538°C maximum (non UL), meets the UL requirements for AWM Style 5107/5335
- TEMPERATURE: 450°C
- VOLTAGE: 600 V

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

Diameters and weights may vary between manufacturers.

Part No.	Conductor Size AWG	No. of Strands	Composite Insulation Thickness (in.)	Braid Thickness (in.)	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.
8TC-1801	18	16	0.025	0.007	0.114	11
8TC-1601	16	26	0.025	0.007	0.127	15
8TC-1401	14	41	0.025	0.007	0.140	21
8TC-1201	12	65	0.025	0.007	0.163	30
8TC-1001	10	105	0.030	0.015	0.214	51
8TC-0801	8	133	0.030	0.015	0.261	75
8TC-0601	6	133	0.030	0.015	0.304	111
8TC-0401	4	133	0.030	0.015	0.360	166

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.