

Type G-GC Lead Cured



Product Description

Heavy duty
EPR insulation
Thermoset CPE jacket
90°C, 2 kV

Applications

For use as flexible power lead with portable or mobile equipment such as pumps, welders, mining machines and mine conveyor equipment.

Specifications

- CONDUCTOR*: Rope-stranded, tinned copper per ASTM B172
- INSULATION: Ethylene Propylene Rubber (EPR) per ICEA S-75-381 (NEMA WC58)
- GROUND AND GROUND CHECK: Stranded, tinned copper
- ASSEMBLY: Three insulated conductors, two ground conductors and one yellow ground check conductor, cabled with fillers
- OVERALL JACKET: Lead cured thermoset compound
- STANDARDS: Meets the requirements of ICEA S-75-381, accepted by MSHA and marked with the manufacturer's P number, CSA C22.2 No. 96 certified
- AMPACITY: Based on an ambient temperature of 40°C and conductor temperature of 90°C per ICEA S-75-381 table. Additional ampacities available in 2008 NEC Table 400.5 (B).
- TEMPERATURE: -50°C to 90°C
- VOLTAGE: 2 kV

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

CV cured available see 5F-XXXXC. Diameters, ground check size and weights may vary among manufacturers.

Part No.	Conductor Size AWG/kcmil	No. of Strands	No. of Conductors	Insulation Thickness (in.)	Ground Wire Size AWG	Ground Check Size AWG	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.	Amps per Conductor
5F-0803	8	133	3	0.060	10	10	0.970	597	59
5F-0603	6	133	3	0.060	10	10	1.050	764	79
5F-0403	4	259	3	0.060	8	10	1.190	1,070	104
5F-0203	2	259	3	0.060	7	10	1.340	1,533	138
5F-0103	1	259	3	0.080	6	8	1.510	1,865	161
5F-1013	1/0	259	3	0.080	5	8	1.650	2,315	186
5F-2023	2/0	259	3	0.080	4	8	1.750	2,750	215
5F-3033	3/0	259	3	0.080	3	8	1.890	3,330	249
5F-4043	4/0	259	3	0.080	2	8	2.040	4,095	287

Conductor color code chart

Number of Conductors	Cable Types	Color Identification	Number of Conductors	Cable Types	Color Identification
2	All	Black, White	4	G Round	Black, White, Red, Orange
3	G or G-GC Round or Flat	Black, White, Red	4	W Round	Black, White, Red, Green
3	SHD-GC	Black, White, Red	5	W Round	Black, White, Red, Green, Orange
3	W Round and Flat	Flat Black, White, Green	Ground Check Conductor	SHD-GC, GGC and MPF-GC	Yellow

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.