

**T-10-NF****Termination Load, 0–3000 MHz**

## General Specifications

Brand	Andrew®
Device Type	Termination Load
Interface	N Female
Color	Black

## Electrical Specifications

Operating Frequency Band	0 – 3000 MHz
Average Power, maximum	10 W
Impedance	50 ohm
Return Loss, minimum	23.0 dB
VSWR	1.15:1

## Mechanical Specifications

Inner Contact Plating	Silver
Outer Contact Plating	Trimetal

## Environmental Specifications

Application	Indoor/Outdoor
Ingress Protection Test Method	IEC 60529:2001, IP65
Operating Temperature	-35 °C to +50 °C (-31 °F to +122 °F)
Relative Humidity	Up to 100%

## Dimensions

Diameter, maximum	35.00 mm		1.38 in
Length	53.50 mm		2.11 in
Net Weight	100.00 g		0.22 lb

## Packed Dimensions

Height	68.0 mm		2.7 in
Length	58.0 mm		2.3 in
Shipping Weight	120.00 g		0.26 lb
Volume	209.0000 mm <sup>3</sup>		
Width	53.0 mm		2.1 in

T-10-NF

POWERED BY



## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2008

### Classification

Above Maximum Concentration Value (MCV)  
Designed, manufactured and/or distributed under this quality management system

